

## Wall-Mount Fiber Optic Distribution Enclosure, 2-Panel Capacity

MODEL NUMBER: **N492-WM2-BK**



Convenient, secure and fully sealed fiber enclosure for managing and protecting your fiber terminations.

### Description

The N492-WM2-BK Wall-Mount Fiber Optic Distribution Enclosure manages and protects your fiber terminations where space is at a premium. It locks using the included key to keep your connections safe from tampering. The doors open wide to reveal plenty of room for splicing and patching your fiber cabling. It supports up to two fiber adapter panels, such as LC (N492-08D-LC), SC (N492-06D-SC) and ST (N492-08S-ST) panels. Cable manager rings, cable ties and a labeling sticker help you keep your cables neatly organized inside the fully sealed enclosure. Made from heavy-duty cold-rolled steel, the N492-WM2-BK mounts on any solid surface.

### Features

#### Fully Sealed Enclosure Manages and Protects Your Fiber Terminations

- Locks with included key to protect connections against tampering
- Mounts securely on any solid surface
- Heavy-duty cold-rolled steel construction
- Includes cable manager rings, cable ties and label for organized cable management
- Supports up to 2 fiber adapter panels, including N492-08D-LC, N492-06D-SC and N492-08S-ST

## Specifications

| OVERVIEW       |                       |
|----------------|-----------------------|
| UPC Code       | 037332202932          |
| Technology     | Multimode; Singlemode |
| Country/Region | Global                |
| PHYSICAL       |                       |
| Color          | Black                 |

### Highlights

- Mounts securely on any solid surface
- Locks with included key to protect connections against tampering
- Made from heavy-duty cold-rolled steel
- Includes rings, ties and label for organized cable management
- Supports up to 2 fiber adapter panels

### Package Includes

- N492-WM2-BK Wall-Mount Fiber Optic Distribution Enclosure, 2-Panel Capacity
- (2) Cable manager rings
- (5) Cable ties
- Cable lock post
- Label
- (2) Keys
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                            |
|--------------------------------------|----------------------------|
| Material of Construction             | NA                         |
| Total Number of Ports                | 0                          |
| Shipping Dimensions (hwd / in.)      | 6.22 x 14.76 x 10.43       |
| Shipping Dimensions (hwd / cm)       | 15.80 x 37.49 x 26.49      |
| Shipping Weight (lbs.)               | 8.20                       |
| Shipping Weight (kg)                 | 3.72                       |
| Unit Dimensions (hwd / in.)          | 0.000 x 0.000 x 0.000      |
| Unit Dimensions (hwd / cm)           | 12 x 31.3 x 16.4           |
| <b>ENVIRONMENTAL</b>                 |                            |
| Operating Temperature                | -40 to 140 F (-40 to 60 C) |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                            |
| Antibacterial                        | No                         |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                            |
| Product Compliance                   | RoHS                       |
| <b>WARRANTY &amp; SUPPORT</b>        |                            |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty  |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.