

SmartPro UPS, Lithium Battery Backup - 120V 1500VA / 1440W Line Interactive, 2U, Sine Wave, LCD

MODEL NUMBER: **SMART1500RM2UL**



Lithium UPS protects connected equipment against damage, downtime and data loss due to blackouts, power surges and line noise.

Features

Protects Rack-Mounted Equipment This UPS provides fully regulated sine wave AC output for servers, telecom hardware and other applications where long battery lifespan is critical. Plug your equipment into the eight NEMA 5-15R outlets. Two outlets are switchable, allowing you to power connected equipment on and off remotely to reset or reboot connected equipment or to shed less significant loads to extend battery runtime for more critical equipment. All outlets are protected by 570-joule network-grade surge protection to fight off damaging power surges and spikes.

Superior LiFePO4 Battery Backup Compared to Lead Acid Battery With more than double the service life, three times more charge/discharge cycles and 60% the weight of comparable lead-acid batteries, the LiFePO4 battery features 120 volt battery backup and recharges to 100% capacity in less than two hours.

Automatic Voltage Regulation (AVR) Conserves Battery Power AVR maintains 120V nominal output over input range of 83V–145V without using battery power.

EMI/RFI Line Noise Filtering Keeps Equipment Performing in Top Form Noise filtering removes electromagnetic and radio frequency interference that can disrupt equipment performance.

Multi-Function LCD and Audible Alarms Keep You Informed The front-panel LCD information and configuration screen displays detailed UPS and site power status and operating data, as well as input and output voltage, operating mode, alarm function and additional options. An alarm sounds to warn you of power failure, low battery, overload, UPS fault and remote shutdown conditions. The LCD screen rotates for easy viewing in rack-mount or tower configurations.

Optional Network Management Cards The SMART1500RM2UL is compatible with UPS management cards, such as WEBCARDLX, for detailed monitoring of UPS and site power conditions.

Communications Ports USB and DB9 ports enable unattended shutdown when used with PowerAlert software (available free at tripplite.eaton.com/products/power-alert). EPO port supports emergency shutdown in large facilities.

Highlights

- LiFePO4 battery offers longer life, more cycles and faster recharge
- 97% line-mode efficiency saves energy and operating costs
- 8 NEMA 5-15R outlets—2 switchable via network interface
- 120V NEMA 5-15P input with 10-ft. (3.05 m) power cord to connect to distant outlets
- To use the Auto Probe feature, this product requires a WEBCARDLX network interface (sold separately) running LX firmware update 15.5.2 or later

Applications

- Deliver regulated sine wave output to connected equipment in a network closet or small-business network
- Protect point-of-sale and VoIP networks against power surges and spikes
- Keep your server room operational during short power failures and allow time for safe shutdowns during longer blackouts
- Back up servers, network storage devices, telecom hardware and other applications where long battery lifespan is critical
- Provide high-level power protection with a low-maintenance design

Package Includes

- SMART1500RM2UL SmartPro 120V 1.5kVA 1.44kW Line-Interactive Sine Wave UPS
- USB cable
- DB9 cable
- EPO cable
- Rack-mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Versatile Installation OptionsThe SMART1500RM2UL includes hardware for 4-post mounting in 2U of EIA-standard 19-inch rack. This UPS mounts on a wall, 2-post rack or in an upright tower position.

High Efficiency OperationOperating with a high 97% line-mode efficiency, this 1.5kVA UPS system saves BTU heat output and energy costs

Ultimate Lifetime Insurance and 5-Year WarrantyThis UPS system is backed by \$250,000 Ultimate Lifetime Insurance, which covers any connected components (U.S., Canada and Puerto Rico only). It also has a 5-year limited warranty.

Specifications

OVERVIEW	
UPC Code	037332213587
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A (120V)
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	10
UPS Input Cord Length (m)	3.1
Recommended Electrical Service	15A 120V
Maximum Input Amps	12
OUTPUT	
Output Capacity (VA)	1500
Output Capacity (kVA)	1.5
Output Capacity (Watts)	1440
Output Capacity (kW)	1.44
Power Factor	0.96
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-14%, +6%
Output Voltage Regulation (Battery Mode)	+/- 5%
Load Management Receptacles	Two switchable single-outlet load banks
Output AC Waveform (AC Mode)	Pure Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave



Powering Business Worldwide

TRIPP LITE
SERIES

Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	Yes
BATTERY	
Battery Type	Lithium-ion (LiFePO4)
Runtime Full Load (min.)	7.1 min. (1440W)
Runtime Half Load (min.)	15.4 min. (720W)
Expandable Runtime	No
DC System Voltage (VDC)	48
Battery Recharge Rate (Included Batteries)	1.4 hours from 10% to 90% (typical, full load discharge)
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 145
Overvoltage Correction	Input voltages between 127 and 145 are reduced by 12%
Undervoltage Correction	Input voltages between 108 and 96 are boosted by 12%
Severe Undervoltage Correction	Input voltages between 83 and 95 are boosted by 24%
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
Switches	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
Alarm Cancel Operation	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
Audible Alarm	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
SURGE / NOISE SUPPRESSION	
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	570
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Rackmount
Rack Height	2U
Cooling Method	Fan
Installation Form Factors Supported with Included Accessories	4 post 19 inch rackmount



Powering Business Worldwide

TRIPP LITE
SERIES

Installation Form Factors Supported with Optional Accessories	2 post rackmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM); 2-4 post front rail rackmount (Heavy-Duty-2-post-Front-Mounting-Ear-Kit-UPSHDEARKIT); 4 post rackmount short-depth (4-Post-1U-Universal-Adjustable-Rack-Mount-Shelf-Kit-for-Wall-Mount-Racks~4POSTRAILKITWM); Tower (2U-9U-Tower-Stand-Kit-select-Rack-Mount-UPS-Systems~2-9USTAND); Wallmount (2-Post-Rack-Mount-Wall-Mount-Adapter-Kit-select-Rack-Mount-UPS-Systems~2POSTRMKITWM);
Minimum Required Rack Depth (cm)	58.42
Minimum Required Rack Depth (inches)	23
Optional Mounting Accessory Notes	Optional 2-9USTAND ; enables upright tower UPS placement; 2POSTRMKITWM ; enables wall-mount and 2-post rackmount installation; 4POSTRAILKITWM ; enables installation in 4-post short-depth racks from 14.5 to 23.5 inches (368 to 597mm); UPSHDEARKIT ; enables installation in 2 or 4-post racks using front vertical rails only, without rear support
Primary UPS Depth (mm)	494
Primary UPS Height (mm)	87
Primary UPS Width (mm)	440
Shipping Dimensions (hwd / in.)	10.24 x 25.59 x 27.76
Shipping Dimensions (hwd / cm)	26.01 x 65.00 x 70.51
Shipping Weight (lbs.)	61.07
Shipping Weight (kg)	27.70
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	8.71 x 43.99 x 49.43
UPS Power Module Dimensions (hwd, in.)	3.43 x 17.32 x 19.46
UPS Power Module Weight (kg)	9.58
UPS Power Module Weight (lbs.)	41.780
Unit Dimensions (hwd / in.)	3.430 x 17.300 x 19.270
Unit Weight (lbs.)	41.780
Unit Weight (kg)	9.58
Mounting Details	Included 4POSTRAILKIT mounting bracket enables installation in 4 post racks from 20.5 to 36 inches (521 to 914mm)
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-95% non-condensing
AC Mode BTU / Hr. (Full Load)	130
AC Mode Efficiency Rating (100% Load)	97%



Powering Business Worldwide

TRIPP LITE
SERIES

Audible Noise	50.4 dBA maximum, front side 1m
COMMUNICATIONS	
Network Management Cards	 WEBCARDLXE ; RELAYIOCARD
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
Communications Cable	USB, DB9 and EPO cabling included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite
Network Management Card Description	Network management card optional
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
LINE / BATTERY TRANSFER	
Transfer Time	5 milliseconds (AC to battery mode), 1 millisecond (Battery to AC mode)
Low Voltage Transfer to Battery Power (Setpoint)	83
High Voltage Transfer to Battery Power (Setpoint)	145
FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Auto Probe Monitoring and Reboot (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Remote management; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS; Individually controllable load banks
Grounding Details	Back panel grounding lug
APPLICATIONS	
UPS Applications	Large Network; High-End Desktop/Small Network
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.