


Important Note

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks.

10Gb Duplex Multimode 50/125 OM3 LSZH Fiber Patch Cable (Mini-LC / LC) - Aqua, 2M (6 ft.)**MODEL NUMBER: N836-02M****Highlights**

- Mini-LC to LC Fiber Patch Cable, 2 Meter
- Designed for 10-Gig Ethernet applications...OM3 Rated
- For use with networking hardware employing mini-LC SFP transceivers
- Max 10Gb distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket

Package Includes

- 2M (6-ft.) 10Gb Duplex MMF 50/125 OM3 LSZH Patch Cable (Mini-LC / LC) - Aqua

Features

- Mini-LC to LC Fiber Patch Cable, 2 Meter
- Designed for 10-Gig Ethernet applications...OM3 Rated
- For use with networking hardware employing mini-LC SFP transceivers
- Max 10Gb distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket
- Use with Brocade FC8-64 and other Mini-LC SFP devices

Specifications

| OVERVIEW | |
|----------------------|-----------------------|
| UPC Code | 037332165718 |
| Technology | Multimode |
| Optical Mode | OM3 |
| CONNECTIONS | |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | MINI LC DUPLEX (MALE) |
| Endface Polish | PC |



Powering Business Worldwide

TRIPP LITE
SERIES

| PHYSICAL | |
|---------------------------------|---|
| Cable Jacket Color | Aqua |
| Connector Color | White; Beige |
| Cable Jacket Material | LSZH |
| Cable Jacket Rating | OFNR |
| Clad Diameter (microns) | 125 |
| Core Diameter (microns) | 50 |
| Number of Fibers | 2 |
| Cable Length (ft.) | 6.6 |
| Cable Length (m) | 2.01 |
| Cable Length (in.) | 78.7 |
| Minimum Bend Radius | 20 mm (Dynamic); 10 mm (Static) |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.05 |
| Shipping Weight (kg) | 0.02 |
| Fiber Cable Length | 2M (6.6 ft) |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 5% to 85% RH, Non-Condensing |
| Storage Humidity Range | 35% to 65% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps |
| Attenuation @ 850NM | 3.0 dB/km |
| Insertion Loss | 0.20 dB |
| FEATURES & SPECIFICATIONS | |
| Push/Pull Tabs | No |
| Breakout | No |
| Trunk | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

| | |
|--|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.