


## MTP/MPO Multimode Base-8 Trunk Cable, 24-Strand, 40GB/100GB, 40/100GBASE-SR4, OM4 Plenum-Rated (3xF/3xF), Push/Pull Tab, Magenta, 61 m (200 ft.)

MODEL NUMBER: **N858-61M-3X8-MG**



Premium multimode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density connections between network equipment in telecom rooms and data centers.

### Description

The 61-meter (200-foot) N858-61M-3X8-MG MTP/MPO Multimode Base-8 Trunk Cable supports 40/100 Gb Ethernet speeds and is designed for high-density connections between network equipment in telecommunication rooms and data centers.

With three female MTP/MPO connectors on each end, this OM4-rated multimode fiber optic cable is recommended for high-density fiber patching between data center MDFs (main distribution frames) and IDFs (intermediate distribution frames). It's colored magenta for instant identification as an OM4 cable. Push/pull tab connectors are easily accessible in high-density data center applications and make the cable easy to install and remove with one hand.

The 8-fiber MTP/MPO connectors are about the same size as SC connectors, but are 12 times denser, freeing up rack space for other cables. Optimized for QSFP+ 40GBASE-SR4 and QSFP28 100GBASE-SR4 networks, this cable is tested for low insertion loss and back reflection on every connector and attenuation loss that meets or exceeds current standards. The 5.6-millimeter ruggedized plenum-rated jacket and bend-insensitive fiber are perfect for connecting high-speed network components in ceilings, walls and ducts.

### Features

#### OM4-Rated for 40/100 Gb Ethernet Applications

- Designed to extend high-density connections between network equipment in telecom rooms and data centers
- Recommended for patching between data center MDFs and IDFs
- Optimized for QSFP+ 40GBASE-SR4 and QSFP28 100GBASE-SR4 networks
- Magenta-colored for identification as an OM4 cable

#### MTP/MPO Connectors with Push/Pull Tabs

- 8-fiber female connectors 12 times denser than SC connectors
- Push/pull tab connectors easy to install and remove with one hand
- 100% tested for low insertion loss and back reflection

### Highlights

- Push/pull tab connectors install/remove with one hand
- 8-fiber MTP/MPO connectors with 12x density of SC connectors
- 100% tested for low insertion loss and back reflection
- 50/125 OM4-rated multimode fiber
- Magenta color for easy OM4 identification

### Package Includes

- N858-61M-3X8-MG MTP/MPO Multimode Base-8 Trunk Cable, Magenta, 61 m

**Error-Free Signal Transfer**

- 50/125 duplex glass fiber construction
- Plenum-rated jacket and bend-insensitive fiber perfect for ceilings, walls and ducts

## Specifications

OVERVIEW	
UPC Code	037332200235
Technology	Multimode
Optical Mode	OM4
CONNECTIONS	
Side A - Connector 1	(3) 8F MPO (FEMALE)
Side B - Connector 1	(3) 8F MPO (FEMALE)
Endface Polish	PC
Polarity	Type B (cross)
PHYSICAL	
Cable Jacket Color	Magenta
Connector Color	Magenta; Black
Cable Jacket Material	PVC
Cable Jacket Rating	OFNP
Clad Diameter (microns)	125
Core Diameter (microns)	50
Number of Fibers	24
Cable Length (ft.)	200.1
Cable Length (m)	61.01
Cable Length (in.)	2401.6
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	4.70 x 10.30 x 10.20
Shipping Dimensions (hwd / cm)	11.94 x 26.16 x 25.91
Shipping Weight (lbs.)	4.90
Shipping Weight (kg)	2.22
Fiber Cable Length	61M (200 ft)
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps
Attenuation @ 850NM	3.0 dB/km
Insertion Loss	0.35 dB
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	Yes
Breakout	Yes
Trunk	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.