

SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Mini Rack Enclosure, White

MODEL NUMBER: SRW9UDPW



Secures and organizes 9U of rack equipment up to 20.5 in. deep in network closets and other locations with limited floor space.

Features

Space-Saving 9U Wall-Mount Enclosure Houses 19 in. Rack Equipment up to 20.5 in. Deep This SmartRack® EIA-310 cabinet is designed to house 9U of equipment, such as network switches and patch panels. It's recommended for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable white powder-coated finish, the cabinet has a maximum load capacity of 200 pounds (90.7 kg).

Lockable for Simple and Secure Equipment Access The front door and removable side panels lock securely to help prevent damage, tampering or theft. The reversible front door can open left or right by rotating the cabinet 180 degrees before mounting. Convenient top and bottom access ports allow easy cable routing through the cabinet.

Generous Airflow Keeps Equipment Cool The front door and both sides are ventilated to ensure a constant flow of air that cools rack-mount equipment and helps prevent overheating that can lead to costly downtime. Round ports built into the top and bottom are designed for optional ventilation fans (such as SRFANWM, sold separately) that increase airflow and expel heat.

Easy Enclosure and Equipment Installation This 9U server rack comes fully assembled and ready to mount to the wall with user-supplied hardware. The side panels can be removed for convenient installation, maintenance and replacement of equipment. Front and rear mounting rails adjust independently to accommodate equipment up to 20.5 inches deep, including network switches and patch panels. Hardware for mounting equipment inside the rack is included.

Make It a Mobile Rack Cabinet to Take It Where Best Needed Instead of mounting the 9U enclosure on a wall, you may install optional SRCASTER rolling caster kit (sold separately) to smoothly wheel the rack along the floor to its destination.

Meets Payment Card Industry Standards The SRW9UDPW provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance.

Highlights

- 9U rack constructed from powder-coated steel that stands up to tough environments
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Flow-through ventilation all around keeps equipment cool to maintain top performance
- Ships fully assembled for immediate wall-mounting with user-supplied hardware
- Provides physical equipment and media security required for PCI DSS compliance

Applications

- Store and organize rack-mount equipment in a network wiring closet, retail location, classroom, office or other area where you need equipment to be secure

Package Includes

- SRW9UDPW SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet
- (18) M6 screws
- (18) M6 cage nuts
- (18) M6 cup washers
- (18) 12-24 screws
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332256065
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	White
Rack Height	9U
Rack Depth	Shallow
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	24.41 x 28.75 x 26.57
Shipping Weight (kg)	22.23
Unit Dimensions (hwd / in.)	19.830 x 23.620 x 21.710
Unit Dimensions (hwd / cm)	50.37 x 59.99 x 55.14
Unit Weight (lbs.)	51.8
Unit Weight (kg)	23.50
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.