

## Protect It! 1-Outlet Portable Surge Protector, Direct Plug-In, 750 Joules, Tel/Modem Protection

MODEL NUMBER: TRAVELCUBE



### Highlights

- 1 AC outlet
- Direct plug-in design
- Built-in tel/modem surge protection
- 750 joule rating
- Diagnostic LED displays protection status

### Package Includes

- TRAVELCUBE surge suppressor

### Description

The TRAVELCUBE is designed for convenient portable and economical surge protection. Small and powerful, the TRAVELCUBE features 750 joules and carries \$10K of insurance as well as a lifetime product warranty. Throw it in a briefcase or purse and have quality surge protection wherever you need it — hotel room, dorm, client office — anywhere!

### Features

- Portable wall-mount cube stores easily in any bag or briefcase
- 1 NEMA5-15R AC outlet
- 750 joules of protection shields equipment from harmful surges, spikes and line noise
- Diagnostic LED displays protection status
- Built-in tel/modem surge protection
- UL 1449 rated 3rd Edition
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332118486
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in



Powering Business Worldwide

TRIPP LITE  
SERIES

Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(1) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(1) Yes
Right-Angle Outlets	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	750
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Material of Construction	Plastic
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
Housing Color	Light Gray



Powering Business Worldwide

TRIPP LITE  
SERIES

Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	1.50 x 4.25 x 6.50
Shipping Dimensions (hwd / cm)	3.81 x 10.80 x 16.51
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	3.300 x 2.100 x 0.370
Unit Dimensions (hwd / cm)	3.78 x 5.49 x 7.80
Unit Weight (lbs.)	.17
Unit Weight (kg)	0.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1449; UL 497A; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.