

#### Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

## Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13 - Green Dot, 10A, 125V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P006-L06-HG10



Connects a PC, printer, monitor, scanner or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

#### Features

**Hospital-Grade Power Cable is a Safe Solution for Medical Facilities** This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible equipment with a three-pin C14 inlet in a hospital or other medical facility. It features a locking C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient care vicinities. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

**Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

**Lifetime Warranty** The P006-L06-HG10 is backed by a lifetime warranty, ensuring reliability and performance.

## Specifications

| OVERVIEW             |                                                                |
|----------------------|----------------------------------------------------------------|
| UPC Code             | 037332224729                                                   |
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |

#### Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cable replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

#### Applications

- Connect a mobile cart battery, monitor, computer or printer to a hospital-grade surge protector up to 6-ft. (1.83 m) away in a hospital environment outside patient care vicinities
- Update or replace the standard power cord provided by a device's original manufacturer

#### Package Includes

- P006-L06-HG10 Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                              |
|--------------------------------------|------------------------------|
| Country/Region                       | North America                |
| <b>INPUT</b>                         |                              |
| Maximum Input Amps                   | 10                           |
| Voltage Compatibility (VAC)          | 125                          |
| <b>CONNECTIONS</b>                   |                              |
| Side A - Connector 1                 | NEMA 5-15P-HG                |
| Side B - Connector 1                 | IEC-320-C13 - LOCKING        |
| <b>PHYSICAL</b>                      |                              |
| Plug Color                           | Black                        |
| Cable Jacket Color                   | Black                        |
| Cable Jacket Material                | PVC                          |
| Cable Jacket Rating                  | VW-1                         |
| Power Cord Jacket Type               | SJT                          |
| Cable Outer Diameter (OD)            | 7.7mm                        |
| Number of Conductors                 | 3                            |
| Wire Gauge (AWG)                     | 18                           |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                         |
| Cable Length (ft.)                   | 6                            |
| Cable Length (m)                     | 1.83                         |
| Shipping Dimensions (hwd / in.)      | 1.00 x 7.00 x 10.00          |
| Shipping Dimensions (hwd / cm)       | 2.54 x 17.78 x 25.40         |
| Shipping Weight (lbs.)               | 0.60                         |
| Shipping Weight (kg)                 | 0.27                         |
| <b>ENVIRONMENTAL</b>                 |                              |
| Operating Temperature Range          | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range            | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range             | 0% to 65% RH                 |
| Storage Humidity Range               | 0% to 65% RH                 |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                              |
| Antibacterial                        | No                           |
| Angled Plug                          | No                           |
| High Voltage                         | No                           |
| Locking Plug                         | Yes                          |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Coiled Power Cord                   | No                                  |
| STANDARDS & COMPLIANCE              |                                     |
| Product Certifications              | CSA (Canada); cUL Listed; UL Listed |
| Product Compliance                  | RoHS; REACH                         |
| WARRANTY & SUPPORT                  |                                     |
| Product Warranty Period (Worldwide) | Lifetime limited warranty           |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.