

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Computer Power Cord, NEMA 5-15P to Locking C13 - Heavy-Duty, 15A, 125V, 14 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P007-L03



Computer power cord connects a server, computer, monitor, printer or other device with a C14 inlet to an AC outlet on a PDU.

Features

NEMA 5-15P to C13 Power Cable for Devices That Require a Heavy-Gauge Connection This IEC-320-C13 to NEMA 5-15P power cord features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. You can use it to connect a computer, server, monitor, laser printer or drive to a PDU, UPS, surge protector or AC wall outlet. It can also replace or upgrade the standard power cord provided by the device's manufacturer. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Warranty The P007-L03 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332218308
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America

Highlights

- Recommended for powering larger servers, laser printers and other network devices
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, large servers and laser printers to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P007-L03 IEC-320-C13 to NEMA 5-15P Power Cord, Locking C13 Connector, 3 ft., Black



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13 - LOCKING
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	10.00 x 7.09 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.01 x 1.27
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	Yes
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.