

European Computer Power Cord, C7 to Schuko, 2.5A, 250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: **P059-006**



C7 to Schuko EU power cord connects your notebook computer or laptop with a C8 power inlet to a Schuko outlet.

Features

European Computer Power Cord Connects Notebook Computers to a Schuko AC Outlet This C7 to Schuko power cord is designed for connecting a notebook computer, laptop or other device with a C8 inlet to a UPS system, PDU or other Schuko outlet. It is also a durable replacement for a worn-out or lost laptop power cord. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Specifications

OVERVIEW	
UPC Code	037332205421
Device Compatibility	Laptop; Computer; UPS; PDU
Country/Region	Europe
INPUT	
Maximum Input Amps	2
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/16 SCHUKO PLUG
Side B - Connector 1	IEC-320-C7 (NON-POLARIZED)
PHYSICAL	

Highlights

- EU power cable recommended for powering notebooks and laptops with C8 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

Applications

- Connect a laptop or notebook computer to a PDU up to 6 ft. (1.8 m) away in your workstation
- Extend an existing power connection up to 6 ft. (1.8 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

Package Includes

- P059-006 C7 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H03VVH2-F
Number of Conductors	2
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.02
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Weight (lbs.)	0.22
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	12.800 x 8.860 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 140°F (-5° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.