


**Important Note**

USB 3.0 Fiber Transceivers only work in conjunction with network switches.

## USB 3.0 Multimode Fiber Optic Transceiver Ethernet Adapter, 10/100/1000 Mbps, 1310nm, 550m, LC

MODEL NUMBER: U336-MMF-1G-LC



Connects your USB-enabled computer or laptop to a 10/100/1000 Mbps fiber optic network without installing an internal Ethernet card.

**Features**

**Connects Your Laptop or PC to a Wired Fiber Network without an Internet Card Installed** This USB to LC fiber optic Ethernet adapter allows you to instantly connect your computer, laptop, tablet or other USB-compatible device to a wired 10/100/1000 Mbps fiber optic network, even if your device has no NIC (Network Interface Controller) installed. The adapter offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. It transmits data up to 550 meters (1804 feet) from your fiber network using a wavelength of 1310nm.

**Hot-Swappable for Installation Without Network Interruption** This USB 3.0 Multimode Fiber Optic Transceiver Ethernet adapter is fully hot-swappable, so you can install it without a potentially costly network shutdown or device reboot. Just connect the built-in USB cable to your device's USB port (which also powers the adapter), and connect the LC duplex port to a high-speed network switch, router or hub using existing or newly run multimode fiber cable (such as N820-Series, sold separately).

**Delivers Full Gigabit Ethernet Performance with Audio and Video Streaming** The compact USB to Ethernet adapter supports full 1 Gbps network speeds and USB 3.0 speeds, allowing you to transfer data efficiently and stream audio and video. The direct fiber connection minimizes the risk of data leaks and electromagnetic interference (EMI). A blue LED indicates successful Ethernet connection and data transfer. The adapter works with Windows and Microsoft Server operating systems.

## Specifications

| OVERVIEW |              |
|----------|--------------|
| UPC Code | 037332225993 |

**Highlights**

- Connects you to a wired Gigabit Ethernet network when Wi-Fi is weak or unavailable
- Provides 1 Gbps throughput up to 550 meters (1804 feet) via multimode fiber cabling for fast Ethernet browsing
- Supports USB 3.0 speeds up to 5 Gbps to ensure efficient data transfers
- USB 3.0 Fiber Transceiver Ethernet adapter powered via USB, so no external power supply is required
- Works with most laptops and PCs running Windows and Microsoft Servers

**Applications**

- Install an LC duplex port on your Chromebook or PC for the purpose of connecting a multimode Gigabit Ethernet network cable
- Upload data from your notebook or download data from the Ethernet at true 10/100 Mbps speeds
- Replace a malfunctioning Ethernet card on your laptop or computer

**System Requirements**

- Computer or laptop with USB-A port (USB 3.0 is required to attain USB 3.0 speeds)
- Windows (through Win 10), Server (2012 or 2008)
- Network switch

**Package Includes**

- U336-MMF-1G-LC USB 3.0 Ethernet NIC Adapter
- Driver CD
- Quick Start Guide



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |  |
|--|--|
| Mode Type                                    | Multimode  |
| <b>INPUT</b>                                 |  |
| Built-In Cable Length (ft.)                  | 0.51   |
| Built-In Cable Length (m)                    | 0.155  |
| Built-In Cable Length (in.)                  | 6.1  |
| Bus Powered                                  | Yes  |
| <b>CONNECTIONS</b>                           |  |
| Side A - Connector 1                         | USB 3.0 A (MALE)                                     |
| Side B - Connector 1                         | LC DUPLEX (FEMALE)                                   |
| Connector Plating                            | Nickel   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |  |
| LED Indicators                               | Blue (Power/Data)                                    |
| <b>PHYSICAL</b>                              |  |
| Color  | White  |
| Material of Construction                     | ABS, PVC   |
| Cable Jacket Rating                          | VW-1   |
| Shipping Dimensions (hwd / in.)              | 6.18 x 4.37 x 1.54                                   |
| Shipping Weight (lbs.)                       | 0.28   |
| Unit Dimensions (hwd / in.)                  | 0.710 x 2.200 x 1.610                                |
| Unit Packaging Type                          | Box  |
| Unit Weight (lbs.)                           | 0.12   |
| Unit Weight (kg)                             | 0.05   |
| <b>ENVIRONMENTAL</b>                         |  |
| Operating Temperature Range                  | 32° to 131°F (0° to 55°C)                            |
| Storage Temperature Range                    | 32° to 140°F (0° to 60°C)                            |
| Relative Humidity                            | 5% to 90 % RH, Non-Condensing                        |
| <b>COMMUNICATIONS</b>                        |  |
| Network Compatibility                        | 1 Gbps (Gigabit)                                     |
| Wavelength                                   | 1310nm   |
| Transmission Distance                        | 550m   |
| <b>FEATURES &amp; SPECIFICATIONS</b>         |  |
| USB Specification                            | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                                     |
|-------------------------------------|-------------------------------------|
| Remote Wakeup Support               | Yes                                 |
| Driver Required                     | Yes                                 |
| Optical Port                        | LC                                  |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                     |
| Product Compliance                  | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>       |                                     |
| Product Warranty Period (Worldwide) | 3-year limited warranty             |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.