

## DisplayPort Extension Cable with Latch, 4K @ 60 Hz, HDCP 2.2 (M/F), 3 ft. (0.91 m)

MODEL NUMBER: **P579-003**



Extends your existing DisplayPort™ connection by 3 ft. Latching male connector prevents accidental disconnections.

### Features

#### Extends an Existing DisplayPort Cable an Extra 3 Ft.

- Female connector attaches to current DisplayPort cable to add length
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports DisplayPort v1.2, DPCP and HDCP 2.2

#### Latching Male Connector Ensures Continuous A/V Signal

- Prevents cable from coming loose or getting accidentally disconnected
- Easy one-touch release button allows unplugging

#### First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Gold-plated contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Flexible PVC jacket
- Smaller connector footprint than VGA or DVI saves space

### Specifications

OVERVIEW	
UPC Code	037332202000
Product Type	Passive Cable
Technology	DisplayPort

### Highlights

- Supports 4K x 2K video resolutions @ 60 Hz
- Latching DisplayPort plug ensures secure connection
- Molded nickel-plated connectors with gold-plated contacts
- Supports DisplayPort v1.2, DPCP and HDCP 2.2
- Smaller connector footprint than VGA or DVI

### Package Includes

- P579-003 DisplayPort Extension Cable with Latch (M/F), 3 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable Type	Passive
<b>VIDEO</b>	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (FEMALE)
Latching or Gripping Connector	Yes
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	10% to 80% RH, Non-Condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty