



DIMENSIONS:	
A	3.750" ±0.063
B	4.875" ±0.125
C	4.500" ±0.063
D	2.560" ±0.063
E	3.000" ±0.063
F	3.750" ±0.063
G	0.500" ±0.125



NOTE #1: ALL LEADS 12" OUT MIN., STRIPPED .5"
 NOTE #2: ORG & GRN/WHT LEADS ARE INTERNALLY GROUNDED TO THE TRANSFORMER CORE.



ELECTRICAL DATA:			
TESTS	CONDITIONS	ACCEPTANCE CRITERIA	
Iex	@ 120V, 60Hz, BLK - BLK/WHT	280mA	Max.
Sec. N.L.V	@ 120V, 60Hz, BLK - BLK/WHT		
	BRN - WHT =	99.67V	±2%
	BRN - GRY =	109.5V	±2%
	BRN - BRN/WHT =	120.0V	±2%
	RD/WT - RD/YL = RD/YL - RD/WT =	360.7V	±2%
	RED/WHT - RED/WHT =	721.4V	±2%
	RED - RED/YEL = RED/YEL - RED =	333.8V	±2%
	RED - RED =	667.6V	±2%
	RED/YEL - RED/BLU =	62.30V	±2%
	GRN - GRN =	6.557V	±2%
DCR	@ 20°C, BLK - BLK/WHT =	1.397 Ω	±20%
	@ 20°C, BRN - BRN/WHT =	1.527 Ω	±20%
	@ 20°C, RED/WHT - RED/WHT =	32.82 Ω	±20%
	@ 20°C, GRN - GRN =	0.025 Ω	±20%
HIPOT	PRIMARY - SECONDARY	3000V, 60Hz, 1 SEC	

REV.#	REVISION	DATE	HAMMOND MANUFACTURING™ ELECTRONIC DIVISION			
0	RELEASED.	C.I. 09/06/23	52 RANKIN PLACE, WATERLOO, ONTARIO, N2J 3Z5			
			DWG. BY: C. ILIE	CHK'D BY:	TITLE: POWER TRANSFORMER	DWG. NO. 290FEXA
			DATE: 09/06/23	APP'D. BY:		
				DIMENSIONS: IN(X) MM()		

PH # (519) 886-6181
 FAX # (519) 886-9540