

Open Frame 2-Post Wall-Mount Rack (200 lb) *RB-2PW Series*

Fixed-depth open frame wall rack with 200 lb load rating for mounting network and telecom equipment.



RACK BASICS®

A HAMMOND BRAND



Key Features and Benefits

- 14-gauge steel body with 12-gauge rails (200 lb **capacity**) provides reliable support for switches, patch panels, and rack-mounted equipment.
- Fixed wall-mount open frame design (19" rack compatible) provides a simple, space-efficient solution for equipment mounting.
- One (1) pair of 10-32 threaded mounting rails with rack unit indicators supports standard rack equipment and consistent installation. Includes starter hardware pack with (25) 10-32 screws (**SCREW1032-25**) for equipment mounting.
- 18 inches of usable mounting depth supports standard network and telecom equipment.
- Open-rear design allows installation over existing equipment and simplifies cable routing.
- Optional **RB-2PW-EXT** extender increases depth to 25 inches without reducing load capacity.
- Self-squaring knock-down design ships unassembled for easier handling and installation.
- TAA-compliant, manufactured in North America supports government procurement requirements and ensures consistent quality.
- Black powder coat finish (GREENGUARD Gold, TSCA, RoHS compliant) supports indoor air quality and environmental compliance.

The RB-2PW Series open frame wall rack provides a simple and durable solution for mounting 19-inch rack equipment in telecom and IT environments. With a 200 lb load rating and fixed 18-inch depth, it supports patch panels, switches, and network equipment in wall-mounted installations.

Designed for structured cabling and network deployments, the RB-2PW offers open access for cable routing and installation over existing equipment. Its heavy-duty construction and optional depth extender make it a versatile solution for a wide range of applications.

When another product may be a better choice


- When you need an adjustable depth wall bracket, consider our **APB** Series.
- When you need a wall bracket with an integrated shelf, consider our **APBS** Series.
- When you need a hinged or center-swing wall bracket for rear access, consider our **HWMR** Series.



This product is not designed nor intended to be used for non-wall mounted applications.

Part of the Rack Basics® line designed for simple, reliable, and affordable installations.

Gallery



Accessories

- Universal Rack Mount Rails
- Rack Panels for Rack Optimization
- Universal Rack Shelf Fixed Steel (Up to 200 lb Capacity)
- Rack Mount Keyboard & Equipment Shelf
- Adjustable Rack Mount DIN Rail Kit 2U Steel DIN Rail Panel
- Ground Stud Kit
- Vertical Cable Manager for Wall Mount Racks
- Adjustable Rack Shelf
- Clamping Rack Shelf
- Hinged Window Rack Security Cover
- We Manufacture PDUs and Outlet Strips

Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Weight Capacity	Vertical Cable Manager Part No.
	Height	Width	Depth		Height	Width	Depth		
RB-2PW8	18.00	20.00	18.00	8U	14.00	19.00	18.00	200 lbs	WRCM8U4BK
RB-2PW12	28.50	20.00	18.00	12U	21.00	19.00	18.00	200 lbs	WRCM12U4BK
RB-2PW20	40.00	20.00	18.00	20U	35.00	19.00	18.00	175 lbs	WRCM20U4BK

Optional Extender Bracket

Part No.	Description
RB-2PW-EXT	Provides additional seven inches of mounting depth (18" to 25") while maintaining weight load capacity.

What's Inside the Box

Qty Included	Description	Replacement Part No.
1	Pair of Rack Rails	URR8U, URR12U, or URR20U
2	Top and Bottom Cover/Wall Brackets	
1	Assembly Instructions	
8	1/4-20 x 0.5in Screw For Assembly	
8	1/4-20 Kep Nut For Assembly	
8	10-32 x 0.75in Rack Screws For Assembly	SCREW1032-10
25	10-32 x 0.75in Rack Mounting Screws	SCREW1032-25

Swap Your Rails for a Different Height

Replace with Part No.	URR Rack Units	RB-2PW Rack Units
URR8U	8U	4U
URR10U	10U	6U
URR12U	12U	8U
URR14U	14U	10U
URR18U	18U	14U
URR21U	21U	17U

Where the RB-2PW series works best

- Telecom backboards and network demarcation points.
- Network closets requiring higher load capacity without enclosure.
- Wall-mounted installations over existing equipment.

Applications and when to use the RB-2PW series

- Installations requiring higher load capacity in an open frame design (up to 200 lb).
- Applications needing fixed-depth mounting for consistent equipment placement.

- Structured cabling environments with open access requirements.
- Installations where simplicity and strength are prioritized.
- Environments where open access is preferred over enclosed cabinets.
- Deployments requiring installation over existing equipment or infrastructure.
- Installations needing cost-effective, heavy-duty wall-mounted support.

Tags: **Open frame wall rack, wall mount rack 19 inch, fixed wall rack, telecom wall rack, network wall rack, 2 post wall rack, patch panel wall mount, IT wall rack, open wall bracket rack***Data subject to change without notice.*

© 2026. Hammond Manufacturing Ltd. All rights reserved.