

**Product Use in your Country or Municipality**

Standards that govern use of this product vary by country and sometimes municipality. In the United States, this product is not for use in the Patient Care Vicinity, as defined in the National Electric Code (NEC). This product is approved to CSA C22.2/CuL standards and approved for use in Canada. For application guidance and product selection in your country, please consult a [Healthcare Product Specialist](#) or your own expert.

## Safe-IT Medical-Grade Power Strip, UL 1363, 4 Hospital-Grade Outlets, Antimicrobial, 15 ft. (4.57 m) Cord, TAA

MODEL NUMBER: **PS-415-HG**



Medical-grade power strip with patented antimicrobial coating and long 15 ft. cord provides safe, versatile power distribution.

**Description**

The PS-415-HG Medical-Grade Power Strip supplies power outside of patient-care vicinities, such as administrative areas or in resident rooms of long-term care facilities that do not use line-operated electrical equipment for diagnostic, treatment or monitoring purposes. Compliant with UL 1363 specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by an antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

A built-in resettable 15A circuit breaker controls power to all outlets and protects the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The 15-foot (4.6 m) cord provides ample reach to a power source.

Keyhole mounting tabs and flanges make installing this power strip easy. The all-metal housing ensures safety and is guaranteed to last a long time in demanding surroundings.

**Features**

**Power Distribution Outside of Patient-Care Vicinities** Ideal for use in administrative areas and resident rooms with no line-operated electrical equipment for diagnostic, treatment or monitoring purposes 120V, 50/60 Hz power strip complies with UL 1363 specifications

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Versatile Medical-Grade Solution** 4 NEMA 5-15R-HG hospital-grade outlets provide consistent

**Highlights**

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Complies with UL 1363 specifications
- 15 ft. (4.6 m) cord with NEMA 5-15P-HG hospital-grade plug
- Features 4 NEMA 5-15R-HG hospital-grade outlets

**Package Includes**

- PS-415-HG UL 1363 Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 15-ft. (4.57 m) Cord
- Owner's Manual



Powering Business Worldwide

TRIPP LITE  
SERIES

powerRugged, all-metal housing for long life in demanding environments

**Premium Safety Features** Resettable 15A circuit breaker protects against dangerous overloads. Switchless design prevents accidental shut-off.

**Ready to Use Right Out of the Box** Built-in keyhole mounting tabs and flanges make the PS-415-HG easy to install on a variety of surfaces.

## Specifications

OVERVIEW	
UPC Code	037332118479
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Color	White
Material of Construction	Metal



Powering Business Worldwide

TRIPP LITE  
SERIES

Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	Inner outlets = 1.27 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.40 x 5.90 x 10.00
Shipping Dimensions (hwd / cm)	6.10 x 14.99 x 25.40
Shipping Weight (lbs.)	3.00
Shipping Weight (kg)	1.36
Unit Dimensions (hwd / in.)	2.000 x 5.500 x 10.000
Unit Dimensions (hwd / cm)	3.8 x 21.9 x 6.4
Mounting Details	Includes flanges
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

TRIPP LITE  
SERIES

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.