

Important Note

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 6x 15A Hospital-Grade Outlets, Safety Covers, 7 ft. Cord

MODEL NUMBER: PS-607-HG-OEM



Supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

Description

The PS-607-HG-OEM Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and six NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

The power strip is protected by a antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The seven-foot (2.1 m) power cord provides ample reach to the AC power source.

Mounting tabs and flanges let you install the PS-607-HG-OEM on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted. 120V, 50/60 Hz power strip complies with UL 1363A specifications.

Exclusive Antimicrobial Protection Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew. Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Versatile Medical-Grade Solution 6 NEMA 5-15R-HG hospital-grade outlets provide consistent power 7-

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A and NFPA 99 specifications
- 6 NEMA 5-15R-HG outlets with integrated locking safety covers
- 7 ft. (2.1 m) cord with NEMA 5-15P-HG plug reaches nearby outlets

Package Includes

- PS-607-HG-OEM UL 1363A Medical-Grade Power Strip, 7-ft. (2.13 m) cord
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

ft. (2.13 m) power cord with NEMA 5-15P-HG hospital-grade plug provides ample reach to the power source
Rugged, all-metal housing for long life in demanding environments

Premium Safety Features Integrated locking outlet safety covers block access to unused outlets Dual resettable built-in 15A circuit breakers protect against dangerous overloads Switchless design prevents accidental shutoff

Ready to Use Right Out of the Box Built-in mounting tabs and flanges for easy installation on a variety of surfaces

Specifications

OVERVIEW	
UPC Code	037332203649
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	7
Right-Angle Plug	No
Input Cord Length (m)	2.13
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 6
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Housing Color	White
Mounting Holes or Slots	Yes
Outlets Measurement (Center to Center)	1.52 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	14.10 x 2.28 x 6.00
Shipping Dimensions (hwd / cm)	35.81 x 5.79 x 15.24
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	34.93 x 6.35 x 3.81
Unit Weight (lbs.)	2.40
Unit Weight (kg)	1.09
Mounting Details	Includes flanges
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.