


Hospital-Grade Surge Protector with 6 Hospital-Grade Outlets, 10 ft. (3.05 m) Cord, 1050 Joules, UL 1363, Not for Patient-Care Rooms

MODEL NUMBER: **SPS610HGRA**



Need to use a surge suppressor behind a desk or in a confined spot? The SPS610HGRA provides surge suppression with the convenience of a space-saving, right-angle hospital-grade plug for placing the units in confined areas and keyhole mounting tabs and flanges for easy installation.

Features

- 1050-joule AC surge suppression rating
- Rugged all-metal housing withstands years of use without loss of ground path continuity
- 6 NEMA5-15R Hospital-Grade AC outlets
- 10-ft. AC cord with integrated, molded right angle Hospital-Grade NEMA 5-15PHG plug
- Keyhole mounting tabs and flanges
- Switch safety cover prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120 volt, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)
- UL1449 3rd Edition listed
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

Specifications

OVERVIEW

| | |
|----------|--------------|
| UPC Code | 037332167071 |
|----------|--------------|

Highlights

- 6 hospital-grade outlets
- 1050 joule rating
- 10-ft. cord with molded right-angle hospital-grade plug
- All metal housing

Package Includes

- SPS610HGRA Surge Suppressor
- Instruction manual with warranty information



Powering Business Worldwide

TRIPP LITE
SERIES

| INPUT | |
|------------------------------------|---------------------------------|
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Voltage Compatibility (VAC) | 120 |
| Maximum Surge Amps | 19500 |
| Input Plug Type | NEMA 5-15P-HG |
| Input Cord Length (ft.) | 10 |
| Right-Angle Plug | Yes |
| Input Cord Length (m) | 3.05 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (6) 5-15R-HG |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (2) Yes |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Diagnostic LED Details | LINE POWER PRESENT (green) |
| Locking Switch Cover | Locking switch cover |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1050 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) |
| Automatic Shut-Off | Yes |
| DATALINE SURGE SUPPRESSION | |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| Telephone/DSL Protection | No |
| PHYSICAL | |
| Material of Construction | Metal |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|---|
| Power Cord Color | Light Gray |
| Housing Color | White |
| Mounting Holes or Slots | Yes |
| Receptacle Color | White |
| Shipping Dimensions (hwd / in.) | 2.20 x 15.00 x 6.00 |
| Shipping Dimensions (hwd / cm) | 5.59 x 38.10 x 15.24 |
| Shipping Weight (lbs.) | 2.55 |
| Shipping Weight (kg) | 1.16 |
| Unit Dimensions (hwd / in.) | 1.500 x 13.750 x 2.500 |
| Unit Dimensions (hwd / cm) | 3.81 x 34.9 x 6.35 |
| Unit Weight (lbs.) | 3.20 |
| Unit Weight (kg) | 1.45 |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) |
| Storage Temperature Range | 14° to 122°F (-10° to 50°C) |
| Operating Humidity Range | 10% to 90% RH |
| Storage Humidity Range | 5% to 95% RH |
| FEATURES & SPECIFICATIONS | |
| Rotatable Outlets | No |
| Antimicrobial | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | cUL Listed; UL 1449; UL 1363; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.