



NCJ10FE-H

Introducing **Combo E**, the new NEUTRIK Combo connector. The **Combo E** features a flat front face providing a sleek, streamlined appearance. The housing is configurable with two different locking versions (metal latch or retention spring). Equipped with gold-plated contacts, **Combo E** delivers excellent conductivity and resistance to wear. Due to the UL94 V0 material used, flame retardancy is ensured. The vertical design, with a 24mm PCB distance, optimizes space in tight configurations, making it perfect for compact, high-performance applications.

Features & Benefits

- ✓ 24mm Panel distance
- ✓ Flat front face
- ✓ Front panel cut-out compatible with Neutrik XLR A Series and Combo A Series
- ✓ Combined 3 pole XLR receptacle and 1/4"" TRS phone jack for balanced mic and line or instrument inputs in one XLR housing
- ✓ Two Connectors in one housing - substantial cost, material, space and labour saving
- ✓ Very low conductor capacitance - ideal for digital audio

Technical Information

Product	
Title	NCJ10FE-H
Product family	Combo
Connection type	chassis connector
Gender	female

Electrical	
Contact resistance XLR	$\leq 10 \text{ m}\Omega$
Contact resistance JACK	$\leq 20 \text{ m}\Omega$
Dielectric strength	1.5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact XLR	3 A
Rated current per contact JACK	3 A
Rated voltage	< 50 Vac

Mechanical	
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	min. 1000 mating cycles
Panel thickness	1mm (0.04") - 3mm (0.12")
Locking device	Latch lock
Wiring	Horizontal PCB mount
Mounting direction	Rear mounting
Mounting screw	A-screw-1-8

Material	
Contact plating	Gold plating
Contacts	Bronze
Insert	Polyamide (PA66)
Locking element	Steel
Locking element plating	Nickel

Environmental	
Flammability	acc. to UL 94 V-0
Solderability	Complies with IEC 60068-2-20
Temperatur	-30 °C to +80 °C