

4U Wall-Mount Bracket with Shelf for Small Switches and Patch Panels, Hinged

MODEL NUMBER: **SRWO4UBRKTSHLF**



Houses 4U of rack equipment up to 14.75 in. deep, such as network switches, with shelf for non-rack equipment, including routers.

Highlights

- Ideal for home office or small business with no floor space for full-size rack cabinet
- Steel construction with smooth laser-cut edges that won't damage cable jackets
- Supports universal mounting for left- or right-hinging to allow easy cable access
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Included shelf holds non-rack items like routers and tower UPS systems

Package Includes

- 4U wall-mount bracket
- Shelf
- (24) 12-24 mounting screws
- Instruction sheet

Features

Wall-Mount Bracket Is the Ideal Alternative to a Full-Size Rack Cabinet

If you don't have enough equipment to justify the purchase of a full-size rack or you don't have enough space for one, this SmartRack® bracket is the ideal alternative for your home office or small business. Made from heavy-duty laser-cut 14-gauge cold-rolled steel with a durable black powder-coated finish, this 4U wall-mount bracket attaches to the wall of your back office or closet with the included mounting screws.

Hinged Bracket Supports EIA-Standard 19 in. Rack Equipment

The SRWO4UBRKTSHLF houses 4U of compatible 19-inch rack components, including EIA-compliant switches and patch panels by any manufacturer, up to 14.75 inches deep. The 4U wall-mount bracket is hinged to allow open, unrestricted access to equipment and cabling from either the left or right side. Maximum load capacity is 150 pounds (68 kilograms).

Rear Cutout Eases Cable Installations

The 4U bracket features an open cutout in the rear that allows for cable feeds through the wall to streamline installations and reduce cable clutter. The laser-cut metal bracket's surfaces and edges are smooth to reduce wear on cable jackets and patch panel equipment.

Space-Saving Shelf Allows Easy Storage of Non-Rack Components

Install the steel shelf at the top or bottom of the bracket to hold equipment that is not rack-mountable, including Ethernet routers, wireless access points, tower UPS systems and mini switches. No separate rack-mount shelf accessory is needed.

Easy Mounting with the Included Hardware

Rear keyhole mounting slots are 16 inches apart to align with standard wall-stud placement. Stamped horizontal reinforcement ribs on the back of the bracket provide extra stability. The 4U wall-mount bracket comes with 12-24 mounting screws for installing the bracket and rack equipment.

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332262950
Device Compatibility	Network Switch; Patch Panel; Router
Rack Type	Bracket
Accessory Type	Mounting Accessories
PHYSICAL	
Color	Black
Rack Height	4U
Rack Depth	Shallow
Maximum Device Depth (cm)	38.10
Maximum Device Depth (in.)	15
Maximum Device Depth (mm)	381
Unit Dimensions (hwd / in.)	10.680 x 19.860 x 15.000
Unit Dimensions (hwd / cm)	27.127 x 50.444 x 38.100
Unit Weight (lbs.)	19.410
Unit Weight (kg)	8.80
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC 60297-3
Product Compliance	EIA/ECA-310-E; REACH; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.