

Protect It! 6-Outlet Home Computer Surge Protector, 2 ft. (0.61 m) Cord, 180 Joules

MODEL NUMBER: **TLP602**



Highlights

- 6 outlets / 2-ft. (0.61 m) cord
- 180 joule rating

Package Includes

- TLP602 Surge Suppressor
- Instruction manual and warranty information

Description

The TLP602 offers economical AC surge suppression for workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP602 offers six total outlets and two-foot (0.6-meter) cord. AC suppression rated at 180 joules shields equipment from surges and line noise. Attractive gray housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories.

Features

- 6 outlets
- 2-ft. (0.61 m) cord
- Surge suppression rating: 180 joules
- 15 amp resettable circuit breaker
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 4 total transformers
- Keyhole support for wall mounting
- Lighted power switch
- \$2,500 Ultimate Lifetime Insurance (USA and Canada Only)

Specifications

OVERVIEW	
UPC Code	037332095404
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Gauge Type	14 gauge
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	12000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	2
Right-Angle Plug	No
Input Cord Length (m)	0.61
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
Switches	Combination AC circuit breaker and 2 position on/off power switch
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	180
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Gray
Housing Color	Gray



Powering Business Worldwide

TRIPP LITE
SERIES

Mounting Holes or Slots	No
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 87 mm; Distance between slot height = 28 mm
Outlets Measurement (Center to Center)	28.5mm
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	2.00 x 4.00 x 11.20
Shipping Dimensions (hwd / cm)	5.08 x 10.16 x 28.45
Shipping Weight (lbs.)	0.74
Shipping Weight (kg)	0.34
Unit Dimensions (hwd / in.)	1.180 x 1.690 x 9.440
Unit Dimensions (hwd / cm)	3.00 x 4.29 x 23.98
Unit Weight (lbs.)	.57
Unit Weight (kg)	0.26
Input Cord Color	Gray
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$2,500 Ultimate Lifetime Insurance