


ENCODER RESOLUTION: 2000 cpr

ENCODER CONN TABLE		
PIN	LEAD COLOR	SIGNAL
1	YELLOW	CH A
2	YELLOW/WHITE	CH A-
3	BLUE	CH B
4	BLUE/WHITE	CH B-
5	ORANGE	INDEX
6	ORANGE/WHITE	INDEX-
7	--	N/C
8	--	N/C
9	--	N/C
10	--	N/C
11	--	N/C
12	--	N/C
13	RED	+Vcc
14	BLK	GND
15	--	N/C

**9** ENCODER CABLE 3004-257 DETAIL -- REF ONLY.



TOLERANCES		THIRD ANGLE PROJECTION	
DECIMALS: MM (INCH) X.XXX = $\pm$ (.005) X.XX = $\pm 0.13$ (.010) X.X = $\pm 0.25$ (.020)			
ANGLES: MACH. = $\pm 5^\circ$ CHAM. = $\pm 5^\circ$		APPROVALS DRAWN <b>R. JONEZ</b> CHECKED	DATE <b>3/5/14</b>
COMPUTER DATA BASE DRAWING		APPROVED	APPLIED MOTION PRODUCTS, INC.
<b>STEP MOTOR OUTLINE</b>			
<b>B</b>	DWG NO. <b>HT34-504D-YAA</b>	REV <b>B</b>	
SCALE: NONE		SHEET 2 OF 2	