

3-Port USB-C Hub - USB 3.x (5Gpbs) Hub Ports, Gigabit Ethernet, 60W PD Charging, White

MODEL NUMBER: **U460-003-3AG-C**



Adds USB-C PD charging, Gigabit Ethernet and 3 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook or tablet.

Features

Portable USB 3.2 Hub Turns Your Device's USB-C or Thunderbolt 3 Port into a Workstation This USB-C adapter with Power Delivery (PD) Charging expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive and other USB peripherals, powering and charging a PD Charging-compliant mobile device, and connecting to a Gigabit Ethernet network—all at the same time.

PD Charging Port Charges the Connected Chromebook, MacBook Pro or Other Device The USB-C PD charging port provides power and charging to the connected PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone). Connect the device's AC wall charger to the USB-C PD port, which supports power input up to 20V 3A (60W). That's sufficient wattage to fast-charge, sync and power most high-capacity devices, including the MacBook Pro. Note: USB-C PD port does not support Quick Charge (QC).

Connects USB Peripherals and Transfers Data at Fast USB 3.2 Gen 1 Speeds Three USB-A ports transfer data at speeds up to 5 Gbps, which is 10 times faster than USB 2.0, between your device and up to three USB peripherals, such as a flash drive, printer and keyboard/mouse. One dedicated USB-A port provides power output up to 5V 1.5A (5W) for quickly charging a connected device. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. Note: Host must support USB OTG (On-the-Go)

Accesses a Wired Gigabit Ethernet Network The RJ45 port offers access to a Gigabit Ethernet network when Wi-Fi is unavailable or when a wired connection offers faster speeds. Connect using a UTP cable (such as N201-Series Cat6 cables, sold separately. See www.tripplite.eaton.com for details.), and enjoy true 10/100/1000 Mbps Ethernet speeds for fast data transfers.

Reversible USB-C Connector Attaches in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connector plugs into a USB-C or Thunderbolt 3 port in either direction for a fumble-free connection every time.

Ready to Use Right from the Package, So You Can Plug and Play Immediately The plug-and-play USB-C dock is specifically designed for use with the MacBook Pro, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software or drivers. It's smaller than a standard smartphone, making it easy to pack into a pocket, backpack or laptop bag for multiport convenience wherever you go.

Highlights

- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- Power Delivery port provides 3A (60W) power output for charging connected device
- Connects you to a wired 10/100/1000 Ethernet network when Wi-Fi is unavailable
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Save data from your computer to a USB thumb drive or external hard drive
- Access a wired Gigabit Ethernet network in a location with no or spotty Wi-Fi
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Connect a USB microphone/headset to record a podcast or listen to music
- Write a report using a USB keyboard with your tablet or Android phone

System Requirements

- Source device with USB-C or Thunderbolt 3 port
- Ethernet network with speeds up to 1000 Mbps

Package Includes

- U460-003-3AG-C USB 3.2 Gen 1 Portable Hub/Adapter
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332193810
Product Type	Hub
Device Compatibility	Chromebook; Computer; Laptop; Router
Technology	Cat5/5e; Cat6; USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(3) USB A (FEMALE); USB C (FEMALE)
Data Ports Details	(3) USB-A - USB 3.2 Gen 1 (5 Gbps)
NETWORK	
Network Ports	RJ45 (FEMALE)
INPUT	
Bus Powered	Yes
Product Length (in.)	6
Product Length (cm.)	15.24
Product Length (ft.)	0.5
Product Length (m)	0.15
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Source Type	AC Adapter; Bus
Power Consumption (Watts)	2.50
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	20V/3A; 60W



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Number of Ports	5
Ports	1
Ports Detail	Connect to a wired Ethernet network at speeds up to 10/100/1000Mbps (Gigabit)
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(3) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
Connector Style	Straight
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green - Power, Orange - Activity
CHARGING	
Number of Charging Ports	4
Total Charging Watts	60
Charging Port Type	(3) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports	(2) USB-A: 0.9A; (1) USB-A: 5V 1.5A (7.5W); USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	Charge the host laptop or other PD Charging compatible device with up to 20V 3A (60W) via the PD portOne dedicated USB-A port provides up to 5V 1.5A (7.5W) of power output to quickly charge mobile devicesThe remaining two USB-A ports each provide 0.9A charging output
Charging Ports / Amps	(2) 0.9A; (1) 1.5A; (1) 3A
Compatible Devices	Chromebook; Laptop; Smartphone; Tablet
PHYSICAL	
Color	White
Material of Construction	ABS, PVC
Plug Color	White
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.9mm
Cable Length (ft.)	0.36
Cable Length (m)	0.11
Cable Length (in.)	4.33
Cable Length (cm)	11



Powering Business Worldwide

TRIPP LITE
SERIES

Total Number of Ports	5
Shipping Dimensions (hwd / in.)	5.51 x 0.91 x 3.94
Shipping Weight (lbs.)	0.13
Unit Dimensions (hwd / in.)	0.650 x 3.780 x 1.575
Unit Dimensions (hwd / cm)	1.65 x 9.6 x 4.0
Unit Dimensions (hwd / mm)	16.5 x 96 x 40
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
BTUs	8.5 BTU/Hr
Operating Humidity Range	10 - 85 % RH, Non-Condensing
Storage Humidity Range	5 - 90 % RH, Non-Condensing
Power Provided to Connected Device(s)	Up to 20V 3A (60W) Input (USB-C), 5V 1.5A (7.5W) Output USB port
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
IEEE Standards Supported	802.3; 802.3az; 802.3u; 802.3x
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Data Transfer Rate	5 Gbps
Ethernet Support	Yes
UASP Support	Yes
Auto MDIX Support	Yes
Full Duplex Support	Yes
Suspend Mode Support	Yes
Remote Wakeup Support	Yes
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N



Powering Business Worldwide

TRIPP LITE
SERIES

Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.