




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE ECO 6994	5/22/14	J KORDIK
B	ADD LABEL, SPEC CHG/ECO 7060	9/15/14	J KORDIK
C	REVISE SPEC PER ECO 7205	5/8/15	J Kordik
D	ADD UL TO LABEL PER ECO 7330	10/12/15	J KORDIK
E	SPECS REVISED PER ECO 7510	10/19/16	J KORDIK

ENCODER CONNECTOR

CONNECTOR: AMP 172171-1
770835-1 contacts (strip)
VIEWING MATING END

MOTOR POWER CONNECTOR

CONNECTOR: AMP 172167-1
170360-1 contacts (strip)
VIEWING MATING END




ENCODER CONNECTION TABLE

PIN	LEAD COLOR	SIGNAL
1	RED	+5V
2	BLACK	GROUND
3	BROWN	U+
4	BROWN/BLACK	U-
5	GRAY	V+
6	GRAY/BLACK	V-
7	WHITE	W+
8	WHITE/BLACK	W-
9	BLUE/BLACK	A+
10	BLUE	A-
11	GREEN	B+
12	GREEN/BLACK	B-
13	YELLOW	Z+
14	YELLOW/BLACK	Z-
15	SHIELD	SHIELD

MOTOR CONNECTION TABLE


PIN	LEAD COLOR	SIGNAL
1	RED	PHASE U
2	YELLOW	PHASE V
3	BLUE	PHASE W
4	YELLOW/GREEN	GROUND



EXAMPLE OF LABEL

NOTES: UNLESS OTHERWISE SPECIFIED

1. A SHAFT SEAL IS SHIPPED WITH MOTOR, BUT NOT INSTALLED.
2. TIMING LOGIC IS CCW AS VIEWED FROM FRONT SHAFT.
3. MOTOR IS IP65, EXCEPT SHAFT OPENING AND CABLE CONNECTOR.
4. INSTALL INDOORS, AWAY FROM DIRECT SUNLIGHT AND FLAMMABLE GASES.
5. 1000M MAX ALTITUDE.

TOLERANCES		THIRD ANGLE PROJECTION		 APPLIED MOTION PRODUCTS, INC.							
DECIMALS: MM (INCH) X.XXX = ±0.013 (.005) X.XX = ±0.25 (.01) X.X = ±2.5 (0.1) ANGLES: MACH. = ±.5° CHAM. = ±5°				AC SERVO MOTOR							
		APPROVALS		DATE		B		DWG NO. J0200-302-4-000		REV E	
		DRAWN R.JONEZ		5/19/14							
		CHECKED									
COMPUTER DATA BASE DRAWING		APPROVED				SCALE: NONE		SHEET 1 OF 2			




AC SERVO MOTOR

B DWG NO. J0200-302-4-000 REV E

AC SERVOMOTOR SPECIFICATION – PERMANENT MAGNET 8 POLES		
INPUT POWER SUPPLY	VAC	208–240 1/3 PHASE
RATED OUTPUT	W	200
VOLTAGE CONSTANT	V(rms)/K(rpm)±10%	27.2
RATED WINDING CURRENT	A (rms)	1.5
PEAK WINDING CURRENT	A (rms)	4.5
WINDING RESISTANCE	V ±10%@20°C	8.6 LINE–TO–LINE
WINDING INDUCTANCE	mH ±20%	25 LINE–TO–LINE
RATED TORQUE	Nm(kgf–cm)	0.64(6.52)
PEAK TORQUE	Nm(kgf–cm)	1.9(19.37)
TORQUE CONSTANT	Nm/A(rms)±10%	0.432
RATED SPEED	rpm/min	3000
MAXIMUM SPEED	rpm/min	6000
WEIGHT	KG (LBS)	1.1(2.3)
INSULATION CLASS		B 130°C
ENCODER RESOLUTION		2500 LINES/REV.
SHAFT LOAD – AXIAL	N(MAX)	70 N/15LB
SHAFT LOAD – RADIAL	N(MAX)	200 N/45LB
MOTOR RATING	REF NOTE 3	IP65
AMBIENT TEMPERATURE	OPERATING	0 TO 40C°
AMBIENT TEMPERATURE	STORAGE	–20 TO 80C°
AMBIENT HUMIDITY MAX		85%
INERTIA – WITH ENCODER	kg m²	0.0000165

TIMING LOGIC / ENCODER SIGNALS





$$T = \frac{360 \text{ DEGREES}}{2500C/T}$$

$$a, b, c, d = T/4 \pm T/8$$

$$h = T \pm T/2$$

TIMING LOGIC / ENCODER SIGNALS
 (NOT TO SAME SCALE AS OTHER DETAIL)



CONTRACT NO.		 APPLIED MOTION PRODUCTS, INC.			
APPROVALS	DATE	SERVO MOTOR SPECIFICATIONS			
DRAWN <i>R. JONEZ</i>	<i>5/19/14</i>				
CHECKED					
APPROVED					
APPROVED		B	FSCM NO.	DWG NO. J0200-302-4-000	REV E
SCALE: NONE		SHEET 2 OF 2			