

WSX075-3200-R

Electrical Specifications (@25C)

1. Input Voltage rating: 100-240VAC, 50-60Hz
2. Input Voltage range: 90-264VAC
3. Input current: 0.8A(RMS) @ 115VAC
4. Max Inrush Current: 50A @ 115VAC (Cold start)
5. Output Voltage: 7.5VDC
6. Output Current: 3.2A
7. Regulation (line & load): $\pm 5\%$
8. Ripple: 100mVpk-pk Max
9. No load power (stand by): < 100 mW
10. Average Efficiency: 86.5% Typ. Meets minimum level VI efficiency.

Environmental Specifications

1. Operating Temperature Range: 0°C to +45° C @ full load
2. Storage Temperature Range: -20°C to 60°C
3. Humidity: 5% to 95%, Non-condensing

Reliability Specifications

1. Leakage Current: <0.25mA (264VAC)
2. Dielectric Strength (Hi-pot): 4242VDC/3secs., 5mA Max
3. Warranty: 5 years

Mechanical Parameters

Case Type: Thermoplastic molded enclosure.
Output Cord: 18 AWG, 4 Ft. Long Nom.

Safety & EMI

ETL: 4002961 conforms to UL STD: 60950-1. Certified to CSA STD C22.2 No. 60950-1 Class II, Double Insulated
BS: 1363-1:1995 + A1:1997 + A2:2003 + A3:2007
AS/NZS: AS/NZS 60950.1:2011 + A1, AS/NZS 60065:2012
GS (S50311479): EN 60950-1: 2006 + A11+A1+A12+A2
EMI standard: FCC part 15 class B, EN 61204-3:2000
Over voltage and short circuit protected




EISA 2007/CEC Compliance: This power supply meets the minimum efficiency requirements per Department of Energy and California Energy Commission.

RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

Parts with a date code of 2533 or after will exclude the CCC marking and China input plug.


Upon printing, this document is considered “uncontrolled”. Please contact Triad Magnetics’ website for the most current version.



North America




European Union




United Kingdom



Australia/New Zealand



China



Dim.: mm