

BERGQUIST GAP FILLER TGF 4500CVO

September 2023

PRODUCT DESCRIPTION

BERGQUIST GAP FILLER TGF 4500CVO provides the following product characteristics:

Technology	2K Silicone
Appearance (Part A)	White
Appearance (Part B)	Pink
Appearance (cured)	Pink
Components	Two components - requires mixing
Mix Ratio by weight: Part A: Part B	1 : 1
Mix Ratio by volume: Part A: Part B	1 : 1
Product Benefits	<ul style="list-style-type: none"> Thermal conductivity: 4.5 W/mK Extended working time for manufacturing flexibility Controlled Volatile Silicones High dispense throughput Optimized viscosity for automated dispensing processes
Cure	Room temperature or heat cure
Operating Temperature	-60 to 200°C
Application	Thermal material, Liquid gap filler
Typical Applications	<ul style="list-style-type: none"> Power inverter Surface mount power switching EV charger Use between heat generating semiconductor packages and heat sink

BERGQUIST GAP FILLER TGF 4500CVO is a two-part, high performance, thermally conductive, liquid gap filling material. The mixed material will cure at room temperature. Cure can be accelerated with the addition of heat.

BERGQUIST GAP FILLER TGF 4500CVO has controlled volatile outgassing silicones for sensitive applications and high dispensing rate in customer application. This liquid-dispensed material offers infinite thickness variation and impart little and reduced stress on components during assembly. As cured, BERGQUIST GAP FILLER TGF 4500CVO offers a soft, thermally conductive, form-in-place elastomer to fill voids and gaps in the customer assembly.

TYPICAL PROPERTIES OF UNCURED MATERIAL**Part A Properties**

Viscosity, mPa·s (cP):

High shear rate, 1,500 s ⁻¹ , ASTM D5099	20,000
Low shear rate, 1.0 s ⁻¹ , DIN 53019	522,000

Shelf Life @ 25°C, days	180
-------------------------	-----

Part B Properties

Viscosity, mPa·s (cP):

High shear rate, 1,500 s ⁻¹ , ASTM D5099	11,000
Low shear rate, 1.0 s ⁻¹ , DIN 53019	361,000

Shelf Life @ 25°C, days	180
-------------------------	-----

Mixed Properties

Density, ASTM D792, g/cc	3.2
--------------------------	-----

Work Life, ASTM D4473:

@ 25°C, hours	21
@ 50°C, minutes	60
@ 85°C, minutes	3



TYPICAL CURING PERFORMANCE**Cure Schedule (Room Temperature cure)**

48 hours @ 25°C

Alternate Cure Schedule4 hours @ 50°C or
30 minutes @ 85°C

The above cure profile(s) are guideline recommendation(s). These conditions (time and temperature) may vary based on customers' experience and specific application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.

TYPICAL PROPERTIES OF CURED MATERIAL**Physical Properties**

Hardness, Shore 00, ASTM D2240	70
Heat Capacity, ASTM E1269, J/g-K	0.8
Siloxane Content, ΣD4-D10, ASTM F2466, ppm	<300
Flammability, UL 94	V-0

Electrical Properties

Volume Resistivity, ASTM D257, ohm-m	1×10^{11}
Dielectric Strength, ASTM D149, V/mm	10,000
Dielectric Constant, ASTM D150 @ 1,000 Hz	8.1

Thermal Properties

Thermal Conductivity, ASTM D5470, W/(m-K)	4.5
Thermal Impedance @ 40 mil, °C-in ² /W:	
10% Deflection	0.45
20% Deflection	0.38
30% Deflection	0.32

Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 25°C. Storage above 25°C can adversely affect product properties.

Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Henkel Representative.

Conversions

(°C x 1.8) + 32 = °F
kV/mm x 25.4 = V/mil
mm / 25.4 = inches
N x 0.225 = lb/F
N/mm x 5.71 = lb/in
psi x 145 = N/mm ²
MPa = N/mm ²
N·m x 8.851 = lb·in
N·m x 0.738 = lb·ft
N·mm x 0.142 = oz·in
mPa·s = cP

GENERAL INFORMATION

Please consult the Safety Data Sheet (SDS) for safe handling information of this product.

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

CONFIGURATIONS AVAILABLE

Cartridges Kits	50cc, 200cc, 400cc, 1,200cc
Pail Kits	6 gallons

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.



Disclaimer

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product. Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

In case products are delivered by Henkel Corporation,or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 3