

HIGHLIGHTS


FEATURES

- Altech DIN Rails comply with DIN EN60715, EN50022, EN50035, EN50045 standards
- Easy mounting of terminal blocks, power supplies and other control components and devices into panel
- Space saving
- Reduces labor
- 35mm, 32mm and 15mm versions
- 1m and 2m standard length
- Custom length available
- Perforated, unperforated

MATERIAL

- Zinc-plated steel
 - 35x7.5mm
 - 35x15mm
 - 32mm
 - 15mm
- Aluminum
 - 35x7.5mm
- Stainless Steel (Type AISI 304)
 - 35x7.5mm

DIN35 x 7.5



35 mm x
7.5 mm deep

Zinc Plated Steel

Type	Cat. No.	Length	Std. Pk.
Perforated	2511120	2m	20
	2511120/1M	1m	40
Unperforated	2511110	2m	20
	2511110/1M	1m	40


Stainless Steel

Type	Cat. No.	Length	Std. Pk.
Perforated	2511125	2m	20
	2511125/1M	1m	40
Unperforated	2511115	2m	20
	2511115/1M	1m	40

Aluminum

Type	Cat. No.	Length	Std. Pk.
Perforated	2511121	2m	20
	2511121/1M	1m	40
Unperforated	2511111	2m	20
	2511111/1M	1m	40

DIN35 x 15




35 mm x
15 mm deep

Zinc Plated Steel


Type	Cat. No.	Length	Std. Pk.
Perforated	CA701-15/S-2M	2m	20
	CA701-15/S	1m	40
Unperforated	CA701-15-2M	2m	20
	CA701-15	1m	40

Dimensions


Perforated Steel and Stainless




Perforated Steel




Perforated Aluminum



Unperforated Steel



Unperforated



DIN32

32 mm x
15 mm deep

DIN15





15 mm x
5.5 mm deep

Zinc Plated Steel

Type	Cat. No.	Length	Std. Pk.
Perforated	2511160	2m	10
	2511160/1M	1m	20
Unperforated	2511150	2m	10
	2511150/1M	1m	20

Zinc Plated Steel

Type	Cat. No.	Length	Std. Pk.
Perforated	CA601/S	2m	20

Dimensions**Perforated Steel****Perforated Steel****Unperforated Steel**

HIGHLIGHTS

SUPPORT BRACKETS

- Elevate DIN Rail away from panel
- Easier mounting of components
- Suitable for all mounting rails
- Increase wiring access
- 45° version for improved visibility
- Straight brackets available in 3 heights:
 - 1"
 - 2"
 - 3"

MOUNTING

- Brackets mount with 2 screws to any panel or flat surface
- Tapped center hole for DIN Rail mounting

MATERIAL

- Zinc-plated yellow chromated Steel

UNIVERSAL DIN CLIPS

- Clips on to any 35mm/32mm DIN Rail
- Flexible mounting solution
- Mount any component on 32mm/35mm DIN Rail
- Various mounting hole solutions
- Material: zinc-plated steel, Polyamide 66

SPACER

- Increases creepage and clearance distance between terminal blocks
- Segregate different groups of terminal blocks


WARNING LABELS

- Mounted on top of terminal block for visual identification
- Make entire terminal block assembly shock-proof

SUPPORT BRACKETS




Cat. No.	Std. Pk.
CA603	25



Cat. No.	Height	Std. Pk.
CA703	1 in.	25
CA803	2 in.	25
CA903	3 in.	25


UNIVERSAL DIN CLIPS

D35CLIP




Cat. No.	Mounting Hole	Std. Pk.
D35CLIP-M4	M4	100
D35CLIP-M5	M5	100

CMTB35



Cat. No.	Mounting Hole	Std. Pk.
CMTB35	2x4.4 mm 2x5.5 mm	50

CA902



Cat. No.	Std. Pk.
CA902	100


SPACER

CASP



Cat. No.	Dimensions	Std. Pk.
CASP	29 x 43 x 8 mm	50

CDL4U SPACER



Cat. No.	Dimensions	Std. Pk.
CDL4USP	54 x 55.5 x 6 mm	50

WARNING LABELS

Cat. No. Terminal Blocks

		Pack	Std. Pk. Strips	Tags
WLX2.5	CX2.5 Series, CXDL2.5, CXK2.5, CXM2.5	1	20	100
WLX4	CX4 Series, CXF Series, CXK4	1	20	100
WLX6	CX6 Series, CXDB Series	1	20	100
WLX10	CX10 Series	1	20	100
SWL4	CTS4U-N, CDB4, CMDB4	1	20	100
SWL10	CTS6U, CDB6U, CMDB6	1	20	100



Selection Table

DIN Rail Type	CA102	CA202	CA702	CA802	CA103	CA602	CA302	CA402	CA502
35x7.5mm DIN Rail	✓	✓	✓	✓	✓		✓		
35x15mm DIN Rail	✓	✓	✓	✓	✓			✓	
32mm DIN Rail	✓		✓						✓
15mm DIN Rail						✓			



POLYAMIDE 66

CA702




Cat. No.	Dimensions	Std. Pk.
CA702	34 x 44 x 9mm	50

CA802




Cat. No.	Dimensions	Std. Pk.
CA802	32 x 45 x 8mm	50

CA202




Heavy Duty End Stop




Cat. No.	Dimensions	Std. Pk.
CA202	44.5 x 50 x 9.5mm	50

CA102



Cat. No.	Dimensions	Std. Pk.
CA102	46 x 50 x 9mm	50

CA103



Screwless Snap-On

Cat. No.	Dimensions	Std. Pk.
CA103	41 x 35 x 6mm	50

CA602



Cat. No.	Dimensions	Std. Pk.
CA602	20 x 28 x 8mm	50

STEEL

CA302



Cat. No.	Dimensions	Std. Pk.
CA302	27 x 39.5 x 16mm	50

CA402



Cat. No.	Dimensions	Std. Pk.
CA402	27 x 39.5 x 16mm	50

CA502



Cat. No.	Dimensions	Std. Pk.
CA502	25 x 22.5 x 11.5mm	50

HIGHLIGHTS

MOUNTING PINS

- End Stops prevent Terminal Blocks and other DIN Rail components from moving on the rail
- Versions for
 - 35x7.5mm Rail
 - 35x15mm Rail
 - 32mm Rail
 - 15mm Rail
- Heavy Duty End stop **CA102, CA202**
- Screwless End Stop **CA103** (snap on)
- Material:
 - Polyamide
 - Steel

HIGHLIGHTS

FEATURES

- Group identification
- Holders fit standard **MT8** marking tags
- GMH6, GMH7 mounted directly on DIN Rail
- GMH1, GMH2, GMH3, GMH4, GMH5, GMH8 mounted on End Stops
- MT1G, MT2G, can be used with all these holders or can be directly mounted on all end stops
- Material: Polyamide 66

DIN RAIL MOUNT

GMH6



Cat. No.	Dimensions	Std. Pk.
GMH6	46.5 x 44.5 x 9.5mm	50

GMH7



Cat. No.	Dimensions	Std. Pk.
GMH7	46.5 x 44.5 x 19.5mm	50

MOUNT ON END STOP

GMH1

Suitable for
CA602



Cat. No.	Dimensions	Std. Pk.
GMH1	15.8 x 14.6 x 8mm	100

GMH4


Suitable for
CA802



Cat. No.	Dimensions	Std. Pk.
GMH4	16.2 x 14 x 8mm	100

GMH5


Suitable for
CA702



Cat. No.	Dimensions	Std. Pk.
GMH5	13.7 x 14 x 8mm	100

GMH2 / GMH3


Suitable for
CA702 (GMH2)
CA802 (GMH3)



Cat. No.	Dimensions	Std. Pk.
GMH2	23.2 x 14 x 8mm	100
GMH3	23 x 14 x 8mm	100

GMH8 / GMH8N


Suitable for
CA103



Cat. No.	Dimensions	Std. Pk.
GMH8	44.65 x 31.10 x 10mm	100
GMH8N	44.65 x 31.10 x 6mm	100

MTG1 / MTG2

Mountable
on all End Clamps



Cat. No.	Dimensions	Std. Pk.
MTG1	4.3 x 34 x 17.8mm	50
MTG2	4.3 x 34 x 8mm	50

TM5

Suitable for
CXDL Series




Cat. No.	Dimensions	Std. Pk.
TM5	38 x 17 x 5mm	50



- Cost Effective MT marking system for quick and accurate identification
- Push-On Tags fit all Altech DIN Rail mount terminal blocks
- Inserted individually or as strips of 10
- Quick and easy marking
- Blank Marking Tags for customer marking
- Order with horizontal/ vertical imprint
- Standard imprints with consecutive or identical numbers/ characters
- Custom imprint with short lead time
- Supplied in packs of 100 tags/ 10 strips

BLANK MARKING TAGS

Cat No./ Type	Standard Packs			Dimensions	
	Pack	Strips	Tags	H	W
MT2	1	10	100	4.9mm	5.8mm
MT3	1	20	100	5.0mm	10.0mm
MT4	1	10	100	5.0mm	4.8mm
MT5	1	10	100	9.5mm	4.5mm
MT6	1	10	100	9.5mm	5.6mm
MT8	1	10	100	10.5mm	7.5mm
MT9	1	10	100	10.3mm	8.7mm
MT10	1	20	100	10.4mm	9.5mm
MT12	1	20	100	10.4mm	11.4mm
MT16	1	20	100	10.5mm	15.4mm
MT2G	1	10	100	5.0mm	5.0mm
MT2B4	1	10	100	5.8mm	9.1mm
Continuous Tags					
MT6F	1	10	10	9.5mm	60.0mm
MT9F	1	10	10	10.3mm	90.0mm



Blank Marking Tag




Horizontal Imprint



Vertical Imprint

HOW TO ORDER IMPRINTED MARKING TAGS



IMPRINT EXAMPLES FOR MT6

HORIZONTAL

Imprint	Cat. No.	Imprint	Cat. No.
1	MT6/H-1	131-140	MT6/H-131-140
2	MT6/H-2	141-150	MT6/H-141-150
3	MT6/H-3	151-160	MT6/H-151-160
4	MT6/H-4	161-170	MT6/H-161-170
5	MT6/H-5	171-180	MT6/H-171-180
6	MT6/H-6	181-190	MT6/H-181-190
7	MT6/H-7	191-200	MT6/H-191-200
8	MT6/H-8	1-100	MT6/H-1-100
9	MT6/H-9	1-50	MT6/H-1-50
10	MT6/H-10	A	MT6/H-A
1-10	MT6/H-1-10	B	MT6/H-B
11-20	MT6/H-11-20	C	MT6/H-C
21-30	MT6/H-21-30	L1	MT6/H-L1
31-40	MT6/H-31-40	L2	MT6/H-L2
41-50	MT6/H-41-50	L3	MT6/H-L3
51-60	MT6/H-51-60	N	MT6/H-N
61-70	MT6/H-61-70	R	MT6/H-R
71-80	MT6/H-71-80	S	MT6/H-S
81-90	MT6/H-81-90	X	MT6/H-X
91-100	MT6/H-91-100	Y	MT6/H-Y
101-110	MT6/H-101-110	Z	MT6/H-Z
111-120	MT6/H-111-120	Ground Symbol	MT6/H-GRND
121-130	MT6/H-121-130		

VERTICAL

Imprint	Cat. No.	Imprint	Cat. No.
1	MT6/V-1	131-140	MT6/V-131-140
2	MT6/V-2	141-150	MT6/V-141-150
3	MT6/V-3	151-160	MT6/V-151-160
4	MT6/V-4	161-170	MT6/V-161-170
5	MT6/V-5	171-180	MT6/V-171-180
6	MT6/V-6	181-190	MT6/V-181-190
7	MT6/V-7	191-200	MT6/V-191-200
8	MT6/V-8	1-100	MT6/V-1-100
9	MT6/V-9	1-50	MT6/V-1-50
10	MT6/V-10	A	MT6/V-A
1-10	MT6/V-1-10	B	MT6/V-B
11-20	MT6/V-11-20	C	MT6/V-C
21-30	MT6/V-21-30	L1	MT6/V-L1
31-40	MT6/V-31-40	L2	MT6/V-L2
41-50	MT6/V-41-50	L3	MT6/V-L3
51-60	MT6/V-51-60	N	MT6/V-N
61-70	MT6/V-61-70	R	MT6/V-R
71-80	MT6/V-71-80	S	MT6/V-S
81-90	MT6/V-81-90	X	MT6/V-X
91-100	MT6/V-91-100	Y	MT6/V-Y
101-110	MT6/V-101-110	Z	MT6/V-Z
111-120	MT6/V-111-120	Ground Symbol	MT6/V-GRND
121-130	MT6/V-121-130		