

CFTDPR4



connectwell
THE RIGHT CONNECTION

Fan Monitor for 4 fans- With Temp Monitor and Power Redundancy with Fan redundancy.

- Compact & Standard DIN Rail Mounting.
- Individual Fans can be programmed.
- Autosensing/Manual Sensing saves calibration time.
- LED Indication for FAN OK, FAN FAIL, FUSE FAIL & FAN TRIP SET.
- Potential free contact for Fan fault.
- Potential free contact for Temp Fault.
- 3-Wire RTD Interface.
- Display for Temperature Display and programm
- 4-20mA current output, 2 Wire (Internal Configurable)
- Input Fuse protection.
- Power and Fan Redundancy.
- Universal Input Voltage design. (110 - 230VAC)
- Programmable AutoReset functionality.

TECHNICAL DATA

Ambient Operating Temperature	0 to +50 °C
Mounting Possibility	DIN 35/DIN 35-15 Rail
Housing Material	PC
Housing Colour	Grey
Rated Input voltage	100-240 VAC
Power Input	9 VA*
Rated Current/Channel	750 mA
Fuse Fail Indication	Yes
	0
	0 - 99
Fan Monitor Units	4
Fan Rating	230VAC/110VAC**
Fan Failure Alarm contact	Yes
Over Temperature Alarm contact	Yes
PT100 interface	Yes
4-20mA output	Yes - (corrospounding to 0-99 Degree C temp.)

CONNECTION SPECIFICATIONS

Type of Connection	Screw Connection
Min. Wire Size	0.5 mm ²
Max. Wire Size	2.5 mm ²
Min. Wire Size(AWG)	20 mm ²
Max. Wire Size(AWG)	14 mm ²
Screw Size	M3
Wire Stripping Length	7 mm
Approvals	Heilo, worldf

ORDERING INFORMATION

CAT. NO.	DESCRIPTION	NO. OF CHN.	DIM. DET.	STD. PACK
CFTDPR4	Fan Failure Module For 4	4	72 x 90 x 58 (W)	1

ORDERING INFORMATION

CAT. NO.	DESCRIPTION	NO. OF CHN.	DIM. DET.	STD. PACK
	Fans with Temperature Monitor, Power Redundancy		X H X D) mm	

ACCESSORIES

IMAGES	CAT. NO.	DESCRIPTION	STD. PACK
	CA701-1M	Din 35 Rail unslopped 1 meter	50
	CA701-2M	Din 35 Rail unslopped 2 meter	50
	CA701-2M-S	Din 35 Rail slopped 2 meter	50
	CA701-1M-S	Din 35 Rail slopped 1 meter	50
	CA701-15-1M	Din 35 Rail 15 deep unslopped 1 meter	50
	CA701-15-1M-S	Din 35 Rail 15 deep slopped 1 meter	50
	CA701-15-2M	Din 35 Rail 15 deep unslopped 2 meter	50
	CA701-15-2M-S	Din 35 Rail 15 deep slopped 2 meter	50
	SCS0.5/3	Electricians Screwdriver for slopped screws	10
	CA702	End Clamp in Polyamide 66 suitable for Din 32 / Din 35 / Din 35-15 Rails	50


CFTDPR4



connectwell
THE RIGHT CONNECTION

PRODUCT DRAWING

Dimensions



CIRCUIT DIAGRAM

Hello, world!

NOTES

* 230VAC Fans can be connected if the Input voltage is 230VAC and 110VAC fans can be connected if input voltage is 110VAC.

General technical Data

Nominal Input Power - 9VA
 Degree of Protection - IP 20.
 Input Freq - 50/60Hz
 Refer Operating manual for Menu structure.
 Pollution Degree - 2
 Installation Category-II
 Temperature Accuracy: $\pm 3^{\circ}\text{C}$

Safety-
 Withstand Voltage - I/P-O/P, I/P%O/P TO DIN - 2KV
 Fan Protection - Fuse(Internal)

Standards -
 Safety - IEC-61010-1
 EMC - IEC-61326-1 ****, IEC-61000-4-2, IEC-61000-4-3, IEC-61000-4-4, IEC-61000-4-5, IEC-61000-4-6, IEC-61000-4-8, IEC-61000-4-11, CISPR 11

Indications
 Fan Ok - Green
 Fan Fail - Red
 Over Temp - Red
 Fuse Fail - Red
 Isolation Resistance - I/P -O/P: more than 1000Mohms

Weight-250gm

Note -
 * Module input consumption -0.1 A, rest is fan current consumption.
 ** 230VAC Fans can be connected if the Input voltage is 230VAC and 110VAC fans can be connected if input voltage is 110VAC.
 *** - Fan overloa

	RTD
	1 mtr
	PT100
Operating Temperature Range	0 TO 99 Degree C.

Fan Rating	
Fan-1A	230VAC / 25-750mA, 110AC / 25-750mA***
Fan-1B	230VAC / 25-750mA, 110AC / 25-750mA***
Fan-2A	230VAC / 25-750mA, 110AC / 25-750mA***
Fan-2B	230VAC / 25-750mA, 110AC / 25-750mA***

Rated Current	5A/250VAC 3A/30VDC
---------------	--------------------

Rated Current	5A/250VAC 3A/30VDC
---------------	--------------------