



[Article Page](#)

Product Description

inductive sensor DC



Name
Order number
Switching distance
Mounting

KJ20-G34KN-DPA
08310000450
20 mm


Switch type

 non shielded
 Changeover
DC PNP

Signal Type
Connection

 Cable

Connection diagramm



D 34 x 60

Dimension (in mm)
Technical Specification
Operating voltage
Max. ripple
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Switching state
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Cable length
Utilisation category
Cable material

10 - 30 V DC
≤ 10 %
2,4 V
200 mA
≤ 13 mA
≤ 10 µA
300
≤ 15 %
-25 ° C to 70 ° C
≤ 10 %
≤ 10 %
LED
yes
yes
yes
IP67
DIN EN 60947-5-2: 2008
2 m
DC 13
PVC LIYY grau



KJ20-G34KN-DPA

Pulsotronic GmbH & Co. KG Neue Schichtstraße 14b 09366 Niederdorf Deutschland +49 (0)37296 930-200

Cable cross

4x0.25 mm²

Errors and omissions exceptet