



[Article Page](#)

Product Description

inductive sensor pressure resistant





Name
Order number
Switching distance
Mounting

Switch type

Signal Type
Connection
Connection diagramm

KJD2-M12EB69-DPÖ-V2/500/17,9
08310002409
2 mm



fine-pitch thread M12 x 69

Dimension (in mm)
Technical Specification
Special features

pressure: 500 bar
length pressure resistant area: 17,9 mm
10 - 30 V DC

Operating voltage
Voltage drop
Max. load current
No load current
Leakage current
Switching frequency
Switching hysteresis
Operating temperature
Temperature drift
Repeat accuracy
Short-circuit proof
Overload protection
Reverse voltage protection
Protection category
EMC-level
Housing material
Utilisation category

2,4 V
200 mA
 ≤ 10 mA
 ≤ 10 μ A
400
 ≤ 15 %
-25 ° C to 100 ° C
 ≤ 10 %
 ≤ 5 %
yes
yes
yes
IP69K
DIN EN 60947-5-2: 2008
Stainless steel V2A
DC 13

Errors and omissions excepted

