

PART  
NAME

NEMA DIE CAST ALUM. ENCLOSURE w/MTG. BRKT

PART  
No.

AN-2810-A &amp; AN-2810-AB

REVISION  
DATE







1/3/2024

UL LISTED FOR U.S. AND CANADA - FILE #E194432

TYPE RATING 4, 4X, 6, 6P, 12 AND 13, COMPARE TO IP-68

80°C. MAXIMUM OPERATING TEMPERATURE

UPDATE REPLACES PART NO. AN-2810 &amp; AN-2810-B

**DRAWING FOR REFERENCE**WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR  
STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES  
PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.**BODY**  
**COVER NOT SHOWN****SECTION A-A****SECTION B-B**MATERIAL: BODY & COVER - ALUMINUM ALLOY #ADC-12  
MOUNTING BRACKET - .09 THK. ALUMINUM (3003-H14)FINISH: NATURAL (SUFFIX -A)  
SMOOTH BLACK POWDERCOAT (SUFFIX -AB)FOUR (4) M4x0.7 x 32mm (1.26") LG. 90°CSK. HEAD  
STAINLESS STEEL SCREWS SUPPLIED FOR ASSEMBLY  
OF COVER TO BODY. APPLY AT 12 IN./LB. OF TORQUE.OUTSIDE AND INSIDE DRAFT ANGLE: 2°  
DIMENSIONS ARE INCH[MM]OPTIONAL ACCESSORIES:  
PCB MOUNTING KIT #57-58  
INTERNAL PANEL #ANX-91310  
REPLACEMENT GASKET #1310GSKTSCGASKET  
(NOT  
INSTALLED)  
MOLDED  
SILICONE GRAY**OPTIONAL INTERNAL PANEL AND  
SUGGESTED PC BOARD LAYOUT**