





REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITAL RELEASE ECO 5096		



ENCODER CONNECTION

PIN#	FUNCTION	COLOR	PIN#	FUNCTION	COLOR
1	A+	BLUE	9	Sens2+	GRAY
2	A-	BLU/BLK	10	Sens2-	GRY/BLK
3	B+	GREEN	11	Sens3+	WHITE
4	B-	GRN/BLK	12	Sens3-	WHT/BLK
5	Z+(index)	YELLOW	13	+5V	RED
6	Z-(index)	YEL/BLK	14	0V	BLACK
7	Sens1+	BROWN	15	DRAIN	W/SHRINK TUBING
8	Sens1-	BRN/BLK	16	N/C	N/A

MOTOR CONNECTION

PIN #	FUNCTION	COLOR
1	A	RED
2	B	WHITE
3	C	BLACK
4	DRAIN	GREEN

2. SEE AMP SPEC NUMBER 200-100-60/23 FOR ELECTRICAL AND PHYSICAL SPECIFICATIONS.

METRIC 60mm

- 1 CLAMP CABLE JACKET/SHRINK TUBING.

TOLERANCES		THIRD ANGLE PROJECTION	
DECIMALS: MM (INCH) X.XXX = ±0.01 (.005) X.XX = ±0.10 (.010) X.X = ±0.20 (.020) ANGLES: MACH. = ±.5° CHAM. = ±5°			
COMPUTER DATA BASE DRAWING		APPROVALS	DATE
		DRAWN S.ARNOLD	03/16/04
		CHECKED	
		APPROVED	
METRIC MOTOR/BRAKE			
B	DWG NO. M0200-151-4-000	REV A	
SCALE: 1/2=1		SHEET 1 OF 1	