

Clamp-type Test Probe

0.64 mm system



Type

KLEPS FP 2B

Makes it possible to contact QFPIC s from 0.5 to 0.8 mm lead pitch. Supplied in pairs (yellow and green). The slim build of the clip make it possible to test QFPIC s with several clips simultaneously. Can be plugged with MKL- and MAL measuring leads.

Clamping range
Clamp type

0.5 - 0.8 mm
Micro grip jaws

PART NO. / Housing color

974101188 ●●



KLEPS 064 PCH

The small weight and the compact design offer the possibility to use it at very small components. Can be plugged with MKL (...) and MAL (...) measuring leads.

1 mm
contact hook

974201100 ●
974201101 ●
974201102 ●
974201103 ●
974201104 ●
974201106 ●
974201107 ○

Technical data

Type of termination
Rated voltage
Measurment cat. acc. to IEC61010
Rated current*

unsprung pin Ø 0.73 mm
30 VAC / 60 VDC
CAT I

Material Specifications

Contact resistance
Contact material
Contact surface material
Housing material

spring steel
nickel
ABS

Environmental conditions

Temperature range

0 °C to +60 °C

Inflamability class

Housing (basic material)

unsprung pin 0.64 mm
30 VAC / 60 VDC
CAT I

contact hook: copper-beryllium,
pin: phosphor bronze
gold

0 °C to +70 °C

Drawing

Measurements are shown in millimeters.
Multiply by 0.03937 to convert to inches.

