


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	Updated Graphics	07-31-26	LY



NOTES:

- CABLE: UL20276
(30AWG*1PR+EAM)*2C+30AWG*1PR+24AWG*2C+AEB (AL) 65%
OUTER JACKET: BLACK, OD: 5.5 ± 0.2mm
- CONNECTOR: USB 3.0 A TYPE MALE 9P
INSULATOR: BLUE
PIN G/F
NICKEL PLATED SHELL
- CONNECTOR: USB 3.0 B TYPE MALE 9P
INSULATOR: BLUE
PIN G/F
NICKEL PLATED SHELL
- PVC MOLDED: 45P BLACK COLOR
- ELECTRICAL TEST:
<1>.100% OPEN SHORT & MISS WIRE TEST
<2>.INSULATION RESISTANCE: AC/DC 300V 10M ohm MIN.
<3>.CONDUCTOR RESISTANCE: 2 ohm MAX.
- 1PC/POLYBAG W/LABEL

CONTROLLED

Dim range (mm)		Tolerance +/- (mm)		Qualtek Electronics Corp. WCI DIVISION		
0-1		0.15		Part Number: 3023015-02M RoHS Compliant		
1-6		0.20		Description: USB 3.0 A/M - USB 3.0 B/M		
6-18		0.30		UNIT: mm REV. B		
18-50		0.50		Drawn / Date Checked / Date Approved / Date		
50-120		0.70		R.Nuti 06-25-10 06-25-10 LY / 06-25-10		
120-250		0.90				
250-500		1.20				