


**Part Number:** 2215YA250472KSTSYX

**Description:** 2215 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 4.7nF  $\pm 10\%$  X7R (2R1) to AEC-Q200

**Approval Specifications:** IEC/EN60384-14:2023  
UL60384-14, CAN/CSA E60384-14:14

**Certification:** TÜV R60186738 / ID1111314114  
UL/cUL E228790-20210208

**Classification:** IEC/EN 60384-14:2023 Class Y2 / X1  
UL/cUL FOWX2, FOWX8



Component Marking and Certification Bodies:

Material Group I : CTI  $\geq 600$



## Mechanical Specification

|                                                       |                                                                                  |
|-------------------------------------------------------|----------------------------------------------------------------------------------|
| Size Code                                             | 2215                                                                             |
| Length (L1) in mm (")                                 | $5.7 \pm 0.40$ ( $0.225 \pm 0.016$ )                                             |
| Width (W) in mm (")                                   | $3.81 \pm 0.35$ ( $0.15 \pm 0.014$ )                                             |
| Thickness (T) in mm (")                               | 2.54 Max (0.1 Max)                                                               |
| Minimum Termination Band (L2,L3) in mm (")            | 0.50 (0.020)                                                                     |
| Maximum Termination Band (L2,L3) in mm (")            | 0.80 (0.030)                                                                     |
| Minimum Band Gap (L4) in mm (") (per IEC/EN 60384-14) | 4.0 (0.158)                                                                      |
| Termination Material                                  | FlexiCap™ Polymer termination, Nickel barrier, Sn Plated Solder (RoHS compliant) |
| Solderability                                         | IEC-60068-2-58                                                                   |
| Packaging                                             | 7" Reel Horizontal Orientation, 500 per reel                                     |

## General Electrical Specification

|                                                       |                                                                   |
|-------------------------------------------------------|-------------------------------------------------------------------|
| Rated Voltage                                         | Class Y2 (250Vac), Class X1 (305Vac), 50/60Hz, 5kV impulse        |
| Humidity Grade                                        | Grade IIIB (IEC/EN60384-14:2023 Annex I)                          |
| Maximum DC Working Voltage                            | 1000Vdc to Annex H / (2500Vdc outside scope of any specification) |
| Nominal Capacitance Value                             | 4.7nF                                                             |
| Capacitance Tolerance                                 | $\pm 10\%$                                                        |
| Tangent of Loss Angle (Tan $\delta$ )                 | $\leq 0.025$                                                      |
| Capacitance and Tan $\delta$ Test Conditions          | 1.0Vrms @ 1kHz                                                    |
| Voltage Proof                                         | 100% test: 4000Vdc 1s min / 5s max                                |
| (50mA max charging current for DC tests. 50% Max, RH) | AQL test: 4000Vdc / 3000Vac 60s min / 5kV 1.2x50 $\mu$ s impulse  |
| Min Insulation Resistance (IR)                        | 100.00GOhm @ 100Vdc                                               |
| Dielectric Classification                             | X7R (2R1) to AEC-Q200                                             |
| Rated Temperature Range                               | -55°C / +125°C                                                    |
| Maximum Capacitance Change over Temperature Range     | No DC Voltage $\pm 15\%$<br>Rated DC Voltage -                    |
| Climatic Category (IEC)                               | 55/125/56                                                         |
| Ageing Characteristic                                 | <2% per decade (nominal capacitance is 1000 hour value)           |

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Monday, August 10, 2026

20260810 201143332UTC

**Part Number:** 2215YA250472KSTSYX

**Description:** 2215 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 4.7nF  $\pm 10\%$  X7R (2R1) to AEC-Q200

## Environmental

|                                                        |                  |
|--------------------------------------------------------|------------------|
| RoHS Compliant to 2011/65/EC as amended by 2015/863/EU | Compliant        |
| REACH Compliant                                        | 253 compliant    |
| California Proposition 65                              | No exposure risk |

## Board Layout


Knowles' conventional 2-terminal chip capacitors can generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover, especially under high humidity conditions. Board cleanliness and environmental conditions can also impact this. Refer to application note AN0043 for further information.

Dimensions given are for guidance. It is ultimately the customers responsibility to confirm that the circuit layout is in accordance with their own product requirements.

### IPC-7351 pad design


|   | 2215   |        |
|---|--------|--------|
| C | 6.00mm | 0.236" |
| Y | 1.50mm | 0.059" |
| X | 4.15mm | 0.163" |



## Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.




## Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness  $> 1.0\text{mm}$ . Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

Application notes with mounting and handling guidance are available on request.



Compex

DLI

Johanson MFG

Novacap

Syfer

Voltronics

### Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com

Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com

[www.knowlescapacitors.com](http://www.knowlescapacitors.com)

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at <http://www.knowlescapacitors.com> or by contacting us.

© The information contained on this drawing is confidential and may not be copied in whole or part in any form or disclosed to a third party without the consent of Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and omissions excepted.

Date: Monday, August 10, 2026

20260810 201143332UTC