

receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 1, IP50, keying: 0, number_of_contacts: 3, solder_cup, contact_type: pins



Basic information

Part number	G11M07-P03MJN0-0070
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	6b86b2

Contact insert description

Special features	high_voltage , iec_60601_1_1_mopp_&_2_moop
Number of contacts	3
Contact type	pins
Contact diameter	2cbf01
Termination type	solder_cup
Termination diameter	cdf846
Wire cross section AWG	a40b26

Technical information

Max. current single contact	744f62	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	10	VDE 0298-4:2003
Test voltage	3.550 V	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	mated: 4.7 mm; unmated: 2.0 mm (Contact to contact)	
Max. creepage distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOOP*	
Max. clearance distance (contact to contact)	mated: 4.7 mm; unmated: 2.0 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOOP*	

safety_text_hv

Mechanical and environmental data


Locking principle	break_away , push_pull
Mating cycles	ebda82
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	4.87 g

Material and surface treatments


Material	psu_gray
Contact material	gold
Color option (Front or back nut)	gray

Insulator materials MEDI-SNAP®
psu_peek_o_a


DIMENSIONS




CODING: 0 °



POSITIONS: 3 positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)