

receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 1, IP50, keying: a, number_of_contacts: 5, pcb, contact_type: sockets, Signal



Basic information

Part number	G11MA7-P05QJ00-0050
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	6b86b2

Contact insert description

Special features	iec_60601_1_1_mopp_&_2_moop
Transmission type	Signal
Number of contacts	5
Contact type	sockets
Contact diameter	2cbf01
Termination type	pcb
Termination diameter	ec72e6

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	5.625	VDE 0298-4:2003
Test voltage	1.05 kV AC	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	0.8 mm (Contact to housing)	
Max. creepage distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	
Max. clearance distance (contact to contact)	0.8 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	

Mechanical and environmental data

Locking principle	break_away , push_pull
Keying	a
Mating cycles	0f8eb4
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	50 °C


Material and surface treatments

Material	psu_gray
Insulator material	peek
Contact material	cu_alloy_with_gold_finish
Color option (Front or back nut)	green


Insulator materials MEDI-SNAP®

psu_peek_o_a


DIMENSIONS




CODING: 40°



POSITIONS: 5 Positions




PCB-LAYOUT:



Borehole 0.8 mm

PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)