


receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 1, IP50, keying: c, number_of_contacts: 3, solder_cup, contact_type: sockets, Signal



Basic information

Part number	G11MC7-P03LPH9-0050
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	6b86b2

Contact insert description

Special features	iec_60601_1_1_mopp_&_2_moop
Transmission type	Signal
Number of contacts	3
Contact type	sockets
Contact diameter	513afe
Termination type	solder_cup
Termination diameter	47dc8e
Wire cross section AWG	e0cfa8

Technical information

Max. current single contact	32a26b	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	12	VDE 0298-4:2003
Test voltage	1.55 kV AC	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	1.2 mm (Contact to housing)	
Max. creepage distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	
Max. clearance distance (contact to contact)	1.2 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	

Mechanical and environmental data

Locking principle	break_away , push_pull
Keying	coding 60°
Mating cycles	ebda82
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	50 °C
Weight	5.29 g


Material and surface treatments

Material	psu_gray
Contact material	gold
Color option (Front or back nut)	green


Insulator materials MEDI-SNAP®

psu_peek_o_a


DIMENSIONS




CODING: 60°



POSITIONS: 3 positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)