


receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 1, IP67, keying: a, number_of_contacts: 6, solder_cup, contact_type: sockets, Signal



Basic information

Part number	G41MA7-P06LFG0-0060
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	6b86b2

Contact insert description

Special features	iec_60601_1_2_mopp_&_2_moop
Transmission type	Signal
Number of contacts	6
Contact type	sockets
Contact diameter	ec72e6
Termination type	solder_cup
Termination diameter	08561d
Wire cross section AWG	374cb3

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	5.625	VDE 0298-4:2003
Test voltage	1.1 kV AC	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	0.65 mm (Contact to housing)	
Max. creepage distance (contact to housing)	IEC 60601-1: 2MOPP, 2MOOP*	
Max. clearance distance (contact to contact)	0.65 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 2MOPP, 2MOOP*	

Mechanical and environmental data

Locking principle	break_away , push_pull
Keying	coding_40°
Mating cycles	ebda82
IP class	IP67
Max. operating temperature	120 °C
Min. operating temperature	-50 °C
Weight	5.93 g


Material and surface treatments

Material	psu_gray
Contact material	gold
Color option (Front or back nut)	blue


Insulator materials MEDI-SNAP®

psu_peek_o_a


CODING: 40°



POSITIONS: 6 Positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)