

**G4TAATO-H005WN-LS00**

ODU AMC® Series T



## Square flange receptacle with break-away, push-pull and screw-lock for front and rear panel mounting

Size: 12 (STD 38999), IP6K8 / IP6K9K, Keying: A, Number of contacts: 5, Solder cup, Contact type: Sockets, Signal

### Basic information



|                    |                     |
|--------------------|---------------------|
| Part number        | G4TAATO-H005WN-LS00 |
| Category           | Connector           |
| Type of connector  | Receptacle          |
| Assembly situation | Flange mounting     |
| Size               | 12 (STD 38999)      |

### Contact insert description

|                        |             |
|------------------------|-------------|
| Transmission type      | Signal      |
| Number of contacts     | 5           |
| Contact type           | Sockets     |
| Contact diameter       | 1.6 mm      |
| Termination type       | Solder cup  |
| Wire cross section AWG | AWG 16 – 20 |

### Technical information

|                             |           |  |
|-----------------------------|-----------|--|
| Max. current single contact | 13 A      | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Test voltage                | 1.8 kV AC | EIA-364-20F:2019-02                        |

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

### Mechanical and environmental data

|                            |                                     |
|----------------------------|-------------------------------------|
| Locking principle          | Break-Away , Push-Pull , Screw-Lock |
| Keying                     | A                                   |
| Mating cycles              | 500                                 |
| IP class                   | IP6K8 / IP6K9K                      |
| Max. operating temperature | 175 °C                              |
| Min. operating temperature | -65 °C                              |
| Tightening torque          | 10 Nm                               |
| Weight                     | 16.4 g                              |

\*IP protection class refers to mated condition

## Material and surface treatments

|                           |                                 |
|---------------------------|---------------------------------|
| <b>Material</b>           | Aluminum with tin-nickel finish |
| <b>Insulator material</b> | PEEK                            |
| <b>Contact material</b>   | Gold                            |


Unless explicitly confirmed otherwise the contact arrangement of an ODU data transmission connector differs from a standard data transmission connector due to the robust ODU specific design. However, the ODU design meets the electrical specifications of the respective standard data transmission protocol.

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).


ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).


CODING:A



POSITIONS: 5 positions



Panel-Cut-out



| Shell Size | Type        | L4   | Φ D2 [mm] | Φ A [mm] |
|------------|-------------|------|-----------|----------|
| 9          | Front panel | 15.1 | 3.25      | 13.1     |
|            | Back panel  |      |           | 15.5     |
| 12         | Front panel | 20.6 | 3.25      | 19.1     |
|            | Back panel  |      |           | 21.2     |

## Further technical information and downloads

[3D-File \(STP File\)](#)