


G11F1C-P06QF00-0000

odu\_mini\_snap®\_series\_f



receptacle\_with\_break\_away\_and\_push\_pull\_locking\_for\_front\_panel\_mounting

size: 1, IP50, keying: 1, number\_of\_contacts: 6, pcb, contact\_type: sockets, Signal



Basic information

|                    |                      |
|--------------------|----------------------|
| Part number        | G11F1C-P06QF00-0000  |
| Category           | connector            |
| Type of connector  | receptacle           |
| Assembly situation | front_panel_mounting |
| Size               | 6b86b2               |

Contact insert description

|                      |         |
|----------------------|---------|
| Transmission type    | Signal  |
| Number of contacts   | 6       |
| Contact type         | sockets |
| Contact diameter     | ec72e6  |
| Termination type     | pcb     |
| Termination diameter | 88d6d3  |

Technical information

|                                              |                             |                                            |
|----------------------------------------------|-----------------------------|--------------------------------------------|
| Max. current single contact                  | 9eeaa1                      | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Max. current insert                          | 4.5                         | VDE 0298-4:2003                            |
| Test voltage                                 | 1.2 kV AC                   | SAE AS 13441:1998 method 3001.1            |
| Max. creepage distance (contact to contact)  | 1.1 mm (Contact to housing) |                                            |
| Max. creepage distance (contact to housing)  | 0.8 mm (Contact to housing) |                                            |
| Max. clearance distance (contact to contact) | 1.1 mm (Contact to contact) |                                            |
| Max. clearance distance (contact to housing) | 0.8 mm (Contact to housing) |                                            |


**Mechanical and environmental data**

|                            |                        |
|----------------------------|------------------------|
| Locking principle          | break_away , push_pull |
| Keying                     | 1                      |
| Mating cycles              | 9e1839                 |
| IP class                   | IP50                   |
| Max. operating temperature | 120 °C                 |
| Min. operating temperature | -40 °C                 |
| Tightening torque          | 2.5 Nm                 |
| Weight                     | 8.77 g                 |


**Material and surface treatments**

|                  |                                  |
|------------------|----------------------------------|
| Material         | cu_alloy_with_matt_chrome_finish |
| Contact material | gold                             |


DIMENSIONS:




CODING:1



POSITIONS: 6 positions




PCB-LAYOUT:



Borehole 0.6 mm

PANEL CUT OUT:



## Further technical information and downloads

[3D-File \(STP File\)](#)