


receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 1, IP50, keying: 0, number_of_contacts: 4, pcb, contact_type: sockets, Signal



Basic information

Part number	G11M07-P04QJ00-0060
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	6b86b2

Contact insert description

Special features	iec_60601_1_1_mopp_&_2_moop
Transmission type	Signal
Number of contacts	4
Contact type	sockets
Contact diameter	2cbf01
Termination type	pcb
Termination diameter	ec72e6

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	7.5	VDE 0298-4:2003
Test voltage	1.3 kV AC	EIA-364-20F:2019-02
Max. creepage distance (contact to contact)	1.2 mm (Contact to housing)	
Max. creepage distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	
Max. clearance distance (contact to contact)	1.2 mm (Contact to contact)	
Max. clearance distance (contact to housing)	IEC 60601-1: 1MOPP. 2MOPP*	

Mechanical and environmental data


Locking principle	break_away , push_pull
Mating cycles	ebda82
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	50 °C
Weight	5.27 g

Material and surface treatments


Material	psu_gray
Contact material	gold
Color option (Front or back nut)	blue

Insulator materials MEDI-SNAP®
psu_peek_o_a


DIMENSIONS




CODING: 0°



POSITIONS: 4 Positions



PCB-LAYOUT:



Borehole 0.8 mm



Further technical information and downloads

[3D-File \[STP File\]](#)