

**G6TAATO-ED08SN-0000**

ODU AMC® Series T



## Receptacle with break-away, push-pull and screw-lock for front and rear panel mounting for bend relief

Size: 9 (STD 38999), IP6K8 / IP6K9K, Keying: A, Number of contacts: 8, Crimp, Contact type: Sockets, Ethernet/IP® (10 Gbit/s)



### Basic information

Part number	G6TAATO-ED08SN-0000
Category	Connector
Type of connector	Receptacle
Assembly situation	Rear panel mounting
Size	9 (STD 38999)

### Contact insert description

Special features	Data transmission
Transmission type	Ethernet/IP® (10 Gbit/s)
Number of contacts	8
Contact type	Sockets
Contact diameter	0.76 mm
Termination type	Crimp
Wire cross section AWG	AWG 22 – 26

### Crimp contacts

Please refer to the installed contacts for the correct crimp settings and the tools to be used.

**[923.000.005.000.292](#)**

### Technical information

Max. current single contact	5 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV AC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

### Cable description

Cable outlet	Overmolding
Min. cable diameter	3
Max. cable diameter	7.6

## Mechanical and environmental data

<b>Locking principle</b>	Break-Away , Push-Pull , Screw-Lock
<b>Keying</b>	A
<b>Mating cycles</b>	500
<b>IP class</b>	IP6K8 / IP6K9K
<b>Max. operating temperature</b>	175 °C
<b>Min. operating temperature</b>	-65 °C
<b>Tightening torque</b>	6 Nm
<b>Weight</b>	11.53 g

\*IP protection class refers to mated condition

## Material and surface treatments

<b>Material</b>	Aluminum with tin-nickel finish
<b>Insulator material</b>	PEEK
<b>Contact material</b>	Gold


Unless explicitly confirmed otherwise the contact arrangement of an ODU data transmission connector differs from a standard data transmission connector due to the robust ODU specific design. However, the ODU design meets the electrical specifications of the respective standard data transmission protocol.

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).


ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).


### DIMENSIONS:




### CODING:A



### POSITIONS: 8 positions



### PANEL CUT OUT:



Further technical information and downloads

Connection diagram	Pos. ODU®	Color	Pos. RJ45®
	1	green-white	3
	2	green	6
	3	brown-white	7
	4	brown	8
	5	blue-white	5
	6	blue	4
	7	orange-white	1
	8	orange	2
housing		shield	housing

[3D-File \(STP File\)](#)

[Assembly Instruction](#)