

## Receptacle with break-away and push-pull locking for front panel mounting

Size: 1, IP50, Keying: 0, Number of contacts: 8, Solder cup, Contact type: Sockets, Signal



### Basic information

|                    |                      |
|--------------------|----------------------|
| Part number        | G91M07-P08LFG0-0000  |
| Category           | Connector            |
| Type of connector  | Receptacle           |
| Assembly situation | Front panel mounting |
| Size               | 1                    |

### Contact insert description

|                        |                               |
|------------------------|-------------------------------|
| Special features       | IEC 60601-1 (2 MOPP & 2 MOPP) |
| Transmission type      | Signal                        |
| Number of contacts     | 8                             |
| Contact type           | Sockets                       |
| Contact diameter       | 0.7 mm                        |
| Termination type       | Solder cup                    |
| Termination diameter   | 0.85 mm                       |
| Wire cross section AWG | AWG 22                        |

Reverse gender on request

### Technical information

|                                              |                             |                                            |
|----------------------------------------------|-----------------------------|--------------------------------------------|
| Max. current single contact                  | 7.5 A                       | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Max. current insert                          | 4.875                       | VDE 0298-4:2003                            |
| Test voltage                                 | 0.95 kV AC                  | EIA-364-20F:2019-02                        |
| Max. creepage distance (contact to contact)  | 0.4 mm (Contact to housing) |                                            |
| Max. clearance distance (contact to contact) | 0.4 mm (Contact to contact) |                                            |

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

## Mechanical and environmental data

|                            |                        |
|----------------------------|------------------------|
| Locking principle          | Break-Away , Push-Pull |
| Mating cycles              | 5.000                  |
| IP class                   | IP50                   |
| Max. operating temperature | 120 °C                 |
| Min. operating temperature | -50 °C                 |
| Weight                     | 5.8 g                  |

\*mated & unmated condition

## Material and surface treatments

|                    |          |
|--------------------|----------|
| Material           | PSU gray |
| Insulator material | PEEK     |
| Contact material   | Gold     |

## Insulator materials MEDI-SNAP®


|                                                | Standard                                      | PEEK                        |
|------------------------------------------------|-----------------------------------------------|-----------------------------|
| Flammability rating                            | UL 94                                         | V-0/1.5                     |
| Operation temperature                          |                                               | -50 to +250 °C              |
| Dielectric strength                            | IEC 60243-1:2013 (VDE 0303-21:2014)           | 19 kV/mm                    |
| Comparative figure of the creep resistance CTI | IEC 60112: 2009 (VDE 0303-11:2010)            | 175                         |
| Water absorption                               | ASTM D 570:1998 / ISO 62:2008                 | 0.1 %                       |
| Insulation resistance                          | IEC 60512-3-1:2002 (DIN EN 60512-3-1:2003-01) | $> 1 \times 10^{12} \Omega$ |

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).


ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).


DIMENSIONS:




CODING: 0 °



POSITIONS: 8 Positions



PANEL CUT OUT:



## Further technical information and downloads

[3D-File \(STP File\)](#)