

receptacle_with_break_away_and_push_pull_locking_for_front_panel_mounting

size: 3, IP50, keying: 0, number_of_contacts: 7, crimp, contact_type: sockets, Signal



Basic information

Part number	G13LOC-P07NSN0-0000
Category	connector
Type of connector	receptacle
Assembly situation	front_panel_mounting
Size	4e0740

Contact insert description

Transmission type	Signal
Number of contacts	7
Contact type	sockets
Contact diameter	c1cfd
Termination type	crimp
Termination diameter	72915d
Wire cross section AWG	30ce77

Technical information

Max. current single contact	fa941e	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	13.65	VDE 0298-4:2003
Test voltage	1.35 kV AC	SAE AS 13441:1998 method 3001.1
Max. creepage distance (contact to contact)	1.1 mm (Contact to housing)	
Max. creepage distance (contact to housing)	1.2 mm (Contact to housing)	
Max. clearance distance (contact to contact)	1.1 mm (Contact to contact)	
Max. clearance distance (contact to housing)	1.2 mm (Contact to housing)	


Mechanical and environmental data

Locking principle	break_away , push_pull
Mating cycles	9e1839
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Tightening torque	6 Nm
Weight	21.1 g


Material and surface treatments

Material	cu_alloy_with_matt_chrome_finish
Contact material	gold


DIMENSIONS:




CODING: 0°



POSITIONS: 7 Positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)