

## receptacle\_with\_break\_away\_and\_push\_pull\_locking\_for\_front\_or\_rear\_panel\_mounting

size: 1, IP50, keying: a, number\_of\_contacts: 6, solder\_cup, contact\_type: sockets, Signal

### Basic information

|                    |                                              |
|--------------------|----------------------------------------------|
| Part number        | G51MA8-P06LFD0-0050                          |
| Category           | connector                                    |
| Type of connector  | receptacle                                   |
| Assembly situation | front_panel_mounting,<br>rear_panel_mounting |
| Size               | 1                                            |

### Contact insert description

|                        |                             |
|------------------------|-----------------------------|
| Special features       | iec_60601_1_1_mopp_&_2_moop |
| Transmission type      | Signal                      |
| Number of contacts     | 6                           |
| Contact type           | sockets                     |
| Contact diameter       | 0.7 mm                      |
| Termination type       | solder_cup                  |
| Termination diameter   | 0.65 mm                     |
| Wire cross section AWG | AWG 26                      |

### Technical information

|                                              |                              |                                            |
|----------------------------------------------|------------------------------|--------------------------------------------|
| Max. current single contact                  | 6 A                          | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Max. current insert                          | 4.5                          | VDE 0298-4:2003                            |
| Test voltage                                 | 1.1 kV AC                    | EIA-364-20F:2019-02                        |
| Max. creepage distance (contact to contact)  | 0.85 mm (Contact to housing) |                                            |
| Max. creepage distance (contact to housing)  | IEC 60601-1: 1MOPP. 2MOOP*   |                                            |
| Max. clearance distance (contact to contact) | 0.85 mm (Contact to contact) |                                            |
| Max. clearance distance (contact to housing) | IEC 60601-1: 1MOPP. 2MOOP*   |                                            |

**Mechanical and environmental data**

|                            |                        |
|----------------------------|------------------------|
| Locking principle          | break_away , push_pull |
| Keying                     | coding_40°             |
| Mating cycles              | 2.000                  |
| IP class                   | IP50                   |
| Max. operating temperature | 120 °C                 |
| Min. operating temperature | -50 °C                 |
| Weight                     | 5.14 g                 |


**Material and surface treatments**

|                                  |           |
|----------------------------------|-----------|
| Material                         | psu_black |
| Contact material                 | gold      |
| Color option (Front or back nut) | green     |


**Insulator materials MEDI-SNAP®**

psu\_peek\_o\_a


DIMENSIONS




CODING: 40°



POSITIONS: 6 Positions



PANEL CUT OUT:



Further technical information and downloads

[3D-File \(STP File\)](#)