

## Receptacle with break-away locking for rear panel mounting

Size: 2, IP6K8 / IP6K9K, Keying: A, Number of contacts: 16, PCB, Contact type: Sockets, HDMI® 1.4 (10.2 Gbit/s)

### Basic information



Part number	GK2YAR-P16UC00-000L
Category	Connector
Type of connector	Receptacle
Assembly situation	Rear panel mounting
Size	2

### Contact insert description

Special features	Data transmission
Transmission type	HDMI® 1.4 (10.2 Gbit/s)
Number of contacts	16
Contact type	Sockets
Contact diameter	0.5 mm
Termination type	PCB
Termination diameter	0.5 mm

Reverse gender on request

### Technical information

Max. current single contact	5 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	2.5	VDE 0298-4:2003
Test voltage	1.2 kV AC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

## Mechanical and environmental data

<b>Locking principle</b>	Break-Away , Push-Pull
<b>Keying</b>	A
<b>Mating cycles</b>	5.000
<b>IP class</b>	IP6K8 / IP6K9K
<b>Max. operating temperature</b>	125 °C
<b>Min. operating temperature</b>	-51 °C
<b>Tightening torque</b>	4 Nm
<b>Weight</b>	10.58 g

\*IP protection class refers to mated condition

## Material and surface treatments

<b>Material</b>	Aluminum with ruthenium finish
<b>Insulator material</b>	PEEK
<b>Contact material</b>	Gold


Unless explicitly confirmed otherwise the contact arrangement of an ODU data transmission connector differs from a standard data transmission connector due to the robust ODU specific design. However, the ODU design meets the electrical specifications of the respective standard data transmission protocol.

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).


ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).


### DIMENSIONS:




### CODING:A




### POSITIONS: 16 positions



### PCB-LAYOUT:



### PANEL CUT OUT:



Further technical information and downloads

Connection diagram	Pos. ODU®	Signal	Pos. HDMI®
	2+	TMDS Data2+	1
	housing	TMDS Data2 Shield	2
	2-	TMDS Data2-	3
	1+	TMDS Data1+	4
	housing	TMDS Data1 Shield	5
	1-	TMDS Data1-	6
	0+	TMDS Data0+	7
	housing	TMDS Data0 Shield	8
	0-	TMDS Data0-	9
	C+	TMDS Clock+	10
	housing	TMDS Clock Shield	11
	C-	TMDS Clock-	12
	14	HEC Data-	19
	13	DDC / CEC / HEC Ground	17
	15	HEC Data+	14
	9	CEC	13
	10	SCL	15
	11	SDA	16
	12	+5V Power	18
	16	-	-
	housing	-	housing

[3D-File \(STP File\)](#)

[Assembly Instruction](#)