

straight_in_line_receptacle_with_break_away_and_push_pull_locking

size: 0, IP50, keying: 2, number_of_contacts: 4, solder_cup, contact_type: sockets, Signal



Basic information

Part number	K10F2C-P04LFG0-5000
Category	connector
Type of connector	in_line_receptacle
Assembly situation	straight
Size	5feceb

Contact insert description

Transmission type	Signal
Number of contacts	4
Contact type	sockets
Contact diameter	ec72e6
Termination type	solder_cup
Termination diameter	08561d
Wire cross section AWG	374cb3

Technical information

Max. current single contact	4232cc	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	7.5	VDE 0298-4:2003
Test voltage	0.9 kV AC	SAE AS 13441:1998 method 3001.1
Max. creepage distance (contact to contact)	0.6 mm (Contact to housing)	
Max. creepage distance (contact to housing)	0.7 mm (Contact to housing)	
Max. clearance distance (contact to contact)	0.6 mm (Contact to contact)	
Max. clearance distance (contact to housing)	0.7 mm (Contact to housing)	

Cable description

Cable outlet	back_nut
Min. cable diameter	4.5
Max. cable diameter	5

Mechanical and environmental data


Locking principle	break_away , push_pull
Keying	2
Mating cycles	9e1839
IP class	IP50
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Weight	9.72 g

Material and surface treatments

Material	cu_alloy_with_matt_chrome_finish
Contact material	gold

Graphics and technical drawings

POSITIONS: 4 positions



Further technical information and downloads

[3D-File \[STP File\]](#)