

Receptacle with screw-lock for rear panel mounting

Size 1, IP6K8 / IP6K9K, Coding B (red), 17 contacts, Sockets, Solder cup, Data transmission



Basic information

Part number	GC1WBM-P17WMM0-000L
Category	Connector
Type of connector	Receptacle
Assembly situation	Rear panel mounting
Size	1

Contact insert description

Special features	Data transmission
Transmission type	HDMI® 1.4 (10.2 Gbit/s)
Number of contacts	17
Contact type	Sockets
Contact diameter	0.3 mm; 0.7 mm
Termination type	Solder cup
Termination diameter	0.45 mm
Wire cross section AWG	AWG 28; AWG 22

Reverse gender on request

Technical information

Max. current single contact	1 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

Mechanical and environmental data

Locking principle	Screw-Lock
Keying	B
Mating cycles	5.000
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	1 Nm
Weight	6.19 g

*IP protection class refers to mated condition





Material and surface treatments

Material	Cu-alloy with ruthenium finish
Insulator material	PEEK
Contact material	Gold

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).



Further technical information and downloads

Connection diagram	Pos. ODU®	Pos. HDMI®	Signal	Color (Pair)	Color (Wire)
	4	9	D0-		Blue
	2	8, 11	Drain wire	Twisted pair blue	Shield
	14	7	D0+		White
	10	4	D1+		Blue
	12	2, 5	Drain wire	Twisted pair silver	Shield
	16	6	D1-		White
	11	1	D2+		Blue
	12	2, 5	Drain wire	Twisted pair red	Shield
	9	3	D2-		White
	3	12	C-		Green
	2	8, 11	Drain wire	Twisted pair green	Shield
	5	10	C+		White
	6	14	HEC D-		Blue
	15	17	Drain wire	Twisted pair gold	Shield
	8	19	HEC D+		White
	7	13	CEC		White
	1	15	SCL		Orange
	13	16	SDA		Yellow
	17	18	+5V Power		Red
	Housing	Shield			Shield

[3D-File \(STP File\)](#)

[Technical specifications](#)