

Receptacle with screw-lock for rear panel mounting

Size 1, IP6K8 / IP6K9K, Coding C (blue), 27 contacts, Sockets, PCB, Data transmission, HDMI® 1.3 (8.13 Gbit/s)



Basic information

Part number	GC1WCM-P27UB00-000L
Category	Connector
Type of connector	Receptacle
Assembly situation	Rear panel mounting
Size	1

Contact insert description

Special features	Data transmission
Transmission type	HDMI® 1.3 (8.13 Gbit/s)
Number of contacts	27
Contact type	Sockets
Contact diameter	0.3 mm
Termination type	PCB
Termination diameter	0.3 mm

Reverse gender on request

Technical information

Max. current single contact	1 A	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	0.4 A	VDE 0298-4:2013
Test voltage	0.75 kV DC	EIA-364-20F:2019-02

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

Mechanical and environmental data

Locking principle	Screw-Lock
Keying	C
Mating cycles	5.000
IP class	IP68 / IP6K9K
Max. operating temperature	125 °C
Min. operating temperature	-51 °C
Tightening torque	1 Nm
Weight	7.4 g

*IP protection class refers to mated condition

Material and surface treatments

Material	Cu-alloy with ruthenium finish
Insulator material	PEEK
Contact material	Gold


Unless explicitly confirmed otherwise the contact arrangement of an ODU data transmission connector differs from a standard data transmission connector due to the robust ODU specific design. However, the ODU design meets the electrical specifications of the respective standard data transmission protocol.

ODU MEDI-SNAP® and MINI-SNAP® are UL-approved (E110586).


ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).


DIMENSIONS:




CODING:C




POSITIONS: 27 positions



PCB-LAYOUT:



PANEL CUT OUT:



Further technical information and downloads

	Pos. ODU®	Signal	Pos. HDMI®
Connection diagram	1	TMDS Data1+	4
	2	-	-
	3	-	-
	4	-	-
	5	TMDS Clock-	12
	6	-	-
	7	-	-
	8	TMDS Data0-	9
	9	-	-
	10	-	-
	11	-	-
	12	-	-
	13	TMDS Data2-	3
	14	-	-
	15	-	-
	16	CEC	13
	17	TMDS Clock+	10
	18	-	-
	19	TMDS Data0+	7
	20	-	-
	21	+5 V	18
	22	TMDS Data2+	1
	23	HEC	14
	24	TMDS Data1-	6
	25	Hot Plug Detect	19
	26	SCL	15
	27	SDA	16

[3D-File \(STP File\)](#)

[Technical specifications](#)