

**straight\_push\_pull\_plug\_for\_bend\_relief**

size: 1, IP50, keying: 0, number\_of\_contacts: 4, solder\_cup, contact\_type: pins, Signal

**Basic information**

|                    |                     |
|--------------------|---------------------|
| Part number        | S21M07-P04MJH0-527S |
| Category           | connector           |
| Type of connector  | plug                |
| Assembly situation | straight            |
| Size               | 6b86b2              |

**Contact insert description**

|                        |                             |
|------------------------|-----------------------------|
| Special features       | iec_60601_1_2_mopp_&_2_moop |
| Transmission type      | Signal                      |
| Number of contacts     | 4                           |
| Contact type           | pins                        |
| Contact diameter       | 2cbf01                      |
| Termination type       | solder_cup                  |
| Termination diameter   | 47dc8e                      |
| Wire cross section AWG | e0cfa8                      |

**Technical information**

|                                              |                             |                                            |
|----------------------------------------------|-----------------------------|--------------------------------------------|
| Max. current single contact                  | 744f62                      | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Max. current insert                          | 10                          | VDE 0298-4:2003                            |
| Test voltage                                 | 1.3 kV AC                   | EIA-364-20F:2019-02                        |
| Max. creepage distance (contact to contact)  | 0.9 mm (Contact to housing) |                                            |
| Max. creepage distance (contact to housing)  | IEC 60601-1: 2MOPP, 2MOOP*  |                                            |
| Max. clearance distance (contact to contact) | 0.9 mm (Contact to contact) |                                            |
| Max. clearance distance (contact to housing) | IEC 60601-1: 2MOPP, 2MOOP*  |                                            |

**Cable description**

|                     |                   |
|---------------------|-------------------|
| Cable outlet        | cable_bend_relief |
| Min. cable diameter | 4                 |
| Max. cable diameter | 5.2               |

**Mechanical and environmental data**

|                            |           |
|----------------------------|-----------|
| Locking principle          | push_pull |
| Mating cycles              | ebda82    |
| IP class                   | IP50      |
| Max. operating temperature | 120 °C    |
| Min. operating temperature | -50 °C    |
| Weight                     | 4.98 g    |


**Material and surface treatments**

|                                  |          |
|----------------------------------|----------|
| Material                         | psu_gray |
| Contact material                 | gold     |
| Color option (Front or back nut) | gray     |


**Insulator materials MEDI-SNAP®**

psu\_peek


## DIMENSIONS



## CODING: 0 °



## POSITIONS: 4 Positions



### Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)