

straight_push_pull_plug

size: 0, IP68, keying: 0, number_of_contacts: 7, solder_cup, contact_type: pins, Signal

**Basic information**

Part number	S30B0C-P07MCC0-3500
Category	connector
Type of connector	plug
Assembly situation	straight
Size	5feceb

Contact insert description

Transmission type	Signal
Number of contacts	7
Contact type	pins
Contact diameter	88d6d3
Termination type	solder_cup
Termination diameter	34856b
Wire cross section AWG	5ef463

Technical information

Max. current single contact	eb211c	IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003)
Max. current insert	2.6	VDE 0298-4:2003
Test voltage	0.9 kV AC	SAE AS 13441:1998 method 3001.1
Max. creepage distance (contact to contact)	0.7 mm (Contact to housing)	
Max. creepage distance (contact to housing)	0.8 mm (Contact to housing)	
Max. clearance distance (contact to contact)	0.7 mm (Contact to contact)	
Max. clearance distance (contact to housing)	0.8 mm (Contact to housing)	

Cable description

Cable outlet	back_nut
Min. cable diameter	3
Max. cable diameter	3.5

Mechanical and environmental data


Locking principle	push_pull
Mating cycles	9e1839
IP class	IP68
Max. operating temperature	120 °C
Min. operating temperature	-40 °C
Weight	17 g

ip_protection_class_refers_to_mated_condition


Material and surface treatments

Material	cu_alloy_with_matt_chrome_finish
Contact material	gold


DIMENSIONS:



CODING: 0 °



POSITIONS: 7 Positions



Further technical information and downloads

[3D-File \[STP File\]](#)

[Assembly Instruction](#)